

SAC-3P-M12MS/5,0-PVC/M12FR OBS - Sensor/actuator cable



1422717

<https://www.phoenixcontact.com/us/products/1422717>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black RAL 9005, Plug straight M12, on Socket angled M12, cable length: 5 m, Without PATGs

Your advantages

- Easy and safe: 100 % electrically tested plug-in components

Commercial data

Item number	1422717
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CBA
GTIN	4055626312170
Weight per piece (including packing)	145.544 g
Weight per piece (excluding packing)	145.544 g
Country of origin	DE

SAC-3P-M12MS/5,0-PVC/M12FR OBS - Sensor/actuator cable



1422717

<https://www.phoenixcontact.com/us/products/1422717>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.4 Nm
-------------------	--------

Connector

Connection 1

Type	Plug straight M12
------	-------------------

Connection 2

Type	Socket angled M12
------	-------------------

SAC-3P-M12MS/5,0-PVC/M12FR OBS - Sensor/actuator cable




1422717

<https://www.phoenixcontact.com/us/products/1422717>

Cable/line

Cable length	5 m
--------------	-----

PVC black [PVC]

Dimensional drawing	
Cable weight	40 kg/km
UL AWM Style	2464 / 1729 (80°C/300 V)
Number of positions	3
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor cross section	3x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.26 mm ±0.05 mm
External cable diameter	4.30 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	3 wires, twisted
Max. conductor resistance	max. 57 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 2500 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	22 mm
Smallest bending radius, movable installation	43 mm
Flame resistance	As per UL-Style 2464
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -10 °C ... 80 °C (Cable, flexible installation)

SAC-3P-M12MS/5,0-PVC/M12FR OBS - Sensor/actuator cable



1422717
<https://www.phoenixcontact.com/us/products/1422717>

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP65
	IP67

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


SAC-3P-M12MS/5,0-PVC/M12FR OBS - Sensor/actuator cable

1422717

<https://www.phoenixcontact.com/us/products/1422717>


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, angled

SAC-3P-M12MS/5,0-PVC/M12FR OBS - Sensor/actuator cable

1422717


<https://www.phoenixcontact.com/us/products/1422717>

Schematic diagram



Pin assignment M12 plug, 3-pos., A-coded, view male side

Schematic diagram



Pin assignment M12 socket, 3-pos., A-coded, view female side


SAC-3P-M12MS/5,0-PVC/M12FR OBS - Sensor/actuator cable



1422717

<https://www.phoenixcontact.com/us/products/1422717>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

SAC-3P-M12MS/5,0-PVC/M12FR OBS - Sensor/actuator cable



1422717
<https://www.phoenixcontact.com/us/products/1422717>

Classifications

ECLASS

ECLASS-13.0	27060311
-------------	----------

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

SAC-3P-M12MS/5,0-PVC/M12FR OBS - Sensor/actuator cable



1422717
<https://www.phoenixcontact.com/us/products/1422717>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com