

# SACB-8/16-M23 - Distributor box



1692844

<https://www.phoenixcontact.com/us/products/1692844>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, application: Standard, connection method: M12 socket Plastic, number of slots: 8, number of positions: 5, coding: A, slot assignment: Double, status display: no, Universal; master cable connection: M23 plug connection 90°, shielding: no

## Your advantages

- Safety in the field, thanks to molded housing and high degree of protection
- Save space: distributor box with double occupancy for two sensors in one slot

## Commercial data

Item number	1692844
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF41
Product key	AF3CBB
Catalog page	Page 114 (PC-2009)
GTIN	4017918177973
Weight per piece (including packing)	152.9 g
Weight per piece (excluding packing)	129 g
Customs tariff number	85366990
Country of origin	DE

# SACB-8/16-M23 - Distributor box



1692844

<https://www.phoenixcontact.com/us/products/1692844>

## Technical data

### Notes

Assembly note	<b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".

### Product properties

Product type	Distributor box
Application	Standard
Number of positions	5
Number of slots	8
Coding	A
LED	no

### Electrical properties

Max. operating voltage $U_{max}$	135 V
Nominal voltage $U_N$	120 V AC
	120 V DC
Rated current, total	12 A
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	4 A

### Connection data

#### Conductor connection

Sensor/actuator connection system	M12 socket
Tightening torque slot sensor/actuator cable	0.4 Nm

#### Pin assignment

Slot/position = Wire color or connection	1 / 4 (A) = 15
	1 / 2 (B) = 7
	2 / 4 (A) = 5
	2 / 2 (B) = 4
	3 / 4 (A) = 16
	3 / 2 (B) = 8
	4 / 4 (A) = 3
	4 / 2 (B) = 14
	5 / 4 (A) = 17
	5 / 2 (B) = 9
	6 / 4 (A) = 2
	6 / 2 (B) = 13

# SACB-8/16-M23 - Distributor box



1692844

<https://www.phoenixcontact.com/us/products/1692844>


7 / 4 (A) = 11
7 / 2 (B) = 10
8 / 4 (A) = 1
8 / 2 (B) = 18
1-8 / 1 (+ 120 V) = 19
1-8 / 3 (0 V) = 6
1-8 / 5 (PE) = 12

## Signaling

Status display present	no
------------------------	----

## Dimensions

Dimensional drawing



Width	54 mm
Height	26 mm
Length	155 mm

## Material specifications

Material Threaded sleeve	PA
Material Housing	PA
Flammability rating according to UL 94	V0
Seal material O-ring	NBR
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA
Material of contact, master cable side	CU alloy
Material of contact surface, master cable side	gold-plated

## Cable/line

Connection method	M23 plug connection
-------------------	---------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-20 °C ... 75 °C


# SACB-8/16-M23 - Distributor box

1692844

<https://www.phoenixcontact.com/us/products/1692844>




## Drawings



1692844


<https://www.phoenixcontact.com/us/products/1692844>

Schematic diagram



M12 slot, socket, 5-pos.

Schematic diagram




M23 plug connection pin, 19-pos.

# SACB-8/16-M23 - Distributor box

1692844

<https://www.phoenixcontact.com/us/products/1692844>

Circuit diagram



# SACB-8/16-M23 - Distributor box



1692844

<https://www.phoenixcontact.com/us/products/1692844>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1692844>

	cUL Recognized			
	Approval ID: E118976			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	120 V	-	22 - 16	-

	UL Recognized			
	Approval ID: E118976			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	120 V	-	22 - 16	-

# SACB-8/16-M23 - Distributor box



1692844

<https://www.phoenixcontact.com/us/products/1692844>

## Classifications

### ECLASS

ECLASS-13.0	27440111
-------------	----------

### ETIM

ETIM 9.0	EC003558
----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------



# SACB-8/16-M23 - Distributor box



1692844

<https://www.phoenixcontact.com/us/products/1692844>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	75d1f016-0a6e-4b9c-8669-091df52ea2a3

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)