

FL SWITCH SFN 6TX/2FX - Industrial Ethernet Switch



2891314

<https://www.phoenixcontact.com/us/products/2891314>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ethernet Switch, 6 TP RJ45 ports, 2 FO ports, 100 Mbps full duplex in SC-D format, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function

Your advantages

- RJ45 ports support a transmission speed of 10/100 Mbps
- Fiber-optic ports support 100 Mbps
- QoS-prioritized (Quality of Service) messages
- The switch also offers cable locking and port blocking
- Local diagnostic indicators with LEDs
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial data

Item number	2891314
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN19
Product key	DNN113
Catalog page	Page 291 (C-6-2019)
GTIN	4046356100854
Weight per piece (including packing)	502.5 g
Weight per piece (excluding packing)	365 g
Customs tariff number	85176200
Country of origin	TW

Technical data

Dimensions

Width	50 mm
Height	120 mm
Depth	70 mm

Material specifications

Housing material	Aluminum
------------------	----------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	6 (RJ45 ports)

Fiber optic interface

Connection method	SC
Transmission speed	100 Mbps (full duplex)
Transmission physics	multi-mode fiberglass
Transmission length	2000 m (Fiberglass 50/125) 2000 m (Fiberglass 62.5/125)
Wavelength	1300 nm
No. of channels	2 (SC multi-mode)

Product properties

Product type	Switch
Product family	Unmanaged Switch SFN
Type	Block design
MTTF	56.8 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Switch functions

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
-----------------	-------------------------------------------------------------------------------------------------

Status and diagnostic indicators	LEDs: U _S , link and activity per port
Additional functions	Autonegotiation
Security functions	
Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode

Electrical properties

Local diagnostics	US1/2 Supply voltage Green LED
	LNK/ACT Link status/data transmission Green LED
	100 Data transmission speed Yellow LED
Maximum power dissipation for nominal condition	5.54 W
Test section	500 V DC 1 min
Transmission medium	Copper
	FO

Supply

Supply voltage (DC)	24 V DC
Supply voltage range	9 V DC ... 32 V DC
Power supply connection	Via COMBICON, max. conductor cross section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Typical current consumption	230 mA (at U _S = 24 V DC)

Connection data

Connection technology

Connection name	Power supply
pluggable	yes

Power supply

Connection method	Screw connection
Conductor cross section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	86 kPa ... 108 kPa (up to 1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)

Resistance to gases that may endanger the functions, in acc. with DIN 40046-36, DIN 40046-37

Sulfur dioxide (SO₂) 10 ±0.3 cm³/m³, hydrogen sulfide (H₂S) 1 ±0.3 cm³/m³, at 25°C and 75% humidity and exposure of four days

Standards and regulations

Free from substances that could impair the application of coating

In acc. with VW specification

EMC data

Electromagnetic compatibility

Conformance with EMC Directive 2004/108/EC

Conformance with EMC directives

IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion B

IEC 61000-4-3 (immunity to radiated interference) Criterion A

IEC 61000-4-4 (burst) Criterion B

IEC 61000-4-5 (surge) Criterion B

IEC 61000-4-6 (immunity to conducted interference) Criterion A

IEC 61000-4-8 (immunity to magnetic fields) Criterion A

EN 55022 (emitted interference) Criterion A

Noise immunity

EN 61000-6-2:2005

Noise emission

Standards/regulations

EN 61000-6-4

System properties

Functionality

Basic functions

Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode

Signaling

Status display

LEDs: U_S, link and activity per port

FL SWITCH SFN 6TX/2FX - Industrial Ethernet Switch



2891314

<https://www.phoenixcontact.com/us/products/2891314>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2891314>



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705



KC

Approval ID: KCC-REI-PCK-FL289131



cUL Listed

Approval ID: FILE E 196811



UL Listed

Approval ID: FILE E 196811

FL SWITCH SFN 6TX/2FX - Industrial Ethernet Switch



2891314

<https://www.phoenixcontact.com/us/products/2891314>

Classifications

ECLASS

ECLASS-13.0	19170402
-------------	----------

ETIM

ETIM 8.0	EC000734
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	57d5f207-e6ac-47ec-af23-bc5f35a54b4c