

# EMT (EX38)R - Insert label



0804547

<https://www.phoenixcontact.com/us/products/0804547>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert label, for marking Festo VTUG-10 valve terminals, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: insert, Number of individual labels: 1, text field height: 38 mm, text field width: 30000 mm

## Your advantages

- EMT (Ex38)R, white insert label, for marking Festo VTUG-10 valve terminals
- Thanks to their special shape, the EMT ... insert labels remain securely inside the collar of the marking groove once inserted
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Marking service: Phoenix Contact can custom-mark all EMT ... markers according to your requirements

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0804547             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 1 pc                |
| Product key                          | BG2411              |
| Catalog page                         | Page 343 (C-3-2019) |
| GTIN                                 | 4055626408385       |
| Weight per piece (including packing) | 415.8 g             |
| Weight per piece (excluding packing) | 415.8 g             |
| Country of origin                    | DE                  |

## Technical data

### Product properties

|                 |                                           |
|-----------------|-------------------------------------------|
| Product type    | Device marking                            |
| Controller type | for marking Festo VTUG-10 valve terminals |

### Marking

|                                     |                            |
|-------------------------------------|----------------------------|
| Number of individual labels         | 1                          |
| Number of individual labels per row | 1                          |
| Identification technology           | Thermal transfer for rolls |

### Mounting

|               |        |
|---------------|--------|
| Mounting type | insert |
|---------------|--------|

### Material specifications

|                |                                |
|----------------|--------------------------------|
| RoHS compliant | yes                            |
| Color          | white (RAL 9010)               |
| Material       | Polyester                      |
| Components     | free from silicone and halogen |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### Scratch test for the determining scratch resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 1518-1:2019-10 (following) |
|---------------|---------------------------------------|

#### Tesafilm test

|               |                                  |
|---------------|----------------------------------|
| Specification | DIN EN ISO 2409:2013 (following) |
| Result        | Test passed                      |

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 150 °C (180 °C) | Test passed                     |

#### Wipe resistance of inscriptions

|                                |                                                |
|--------------------------------|------------------------------------------------|
| Specification                  | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|                                | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0] | Test passed                                    |

# EMT (EX38)R - Insert label



0804547

<https://www.phoenixcontact.com/us/products/0804547>

|                                                   |                          |
|---------------------------------------------------|--------------------------|
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed              |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed              |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed              |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed              |
| Specification                                     | ISO 175:2010 (following) |
| Test duration                                     | 168 h                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed              |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed              |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed              |
| IRM 901                                           | Test passed              |
| IRM 902                                           | Test passed              |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## Ambient conditions

|                                                     |                                                                                                         |
|-----------------------------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 120 °C                                                                                       |
| Recommended storage conditions                      | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                                                   |
| Recommended humidity (storage/transport)            | 50 %                                                                                                    |
| Shelf life                                          | 2 years                                                                                                 |

## Dimensions

|                   |          |
|-------------------|----------|
| Width             | 38 mm    |
| Length            | 30000 mm |
| Material strength | 0.25 mm  |

## Text field

|                   |          |
|-------------------|----------|
| Text field width  | 30000 mm |
| Text field height | 38 mm    |

## Standards and regulations

# EMT (EX38)R - Insert label

0804547

<https://www.phoenixcontact.com/us/products/0804547>



|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

# EMT (EX38)R - Insert label



0804547

<https://www.phoenixcontact.com/us/products/0804547>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281106 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# EMT (EX38)R - Insert label



0804547  
<https://www.phoenixcontact.com/us/products/0804547>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)