

PML-T110 (26X280)R - Pipeline marker



1014247

<https://www.phoenixcontact.com/us/products/1014247>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pipeline marker, Roll, blue, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2: pre-printed, mounting type: adhesive, diameter: 0 mm, Number of individual labels: 250, text field height: 26 mm, text field width: 280 mm

Your advantages

- Stick-on pipeline markers, unmarked
- Suitable for indoor and outdoor use
- Pipeline marking according to DIN 2403
- In combination with the PML-GHS hazardous substances labels, marking which conforms to the Ordinance on Hazardous Substances (GefStoffV) can be applied
- High adhesive strength
- Finely perforated arrowheads enable the arrowheads which are not required to be easily removed
- High temperature resistance
- Group 0 (oxygen)

Commercial data

Item number	1014247
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG21
Product key	BG2611
GTIN	4046356784436
Weight per piece (including packing)	494.92 g
Weight per piece (excluding packing)	494.9 g
Customs tariff number	39199080
Country of origin	DE

PML-T110 (26X280)R - Pipeline marker



1014247

<https://www.phoenixcontact.com/us/products/1014247>

Technical data

Product properties

Product type	Plant marker
Area of application	Pipeline labels
	Pipeline identification according to DIN 2403
Type	Rectangle

Marking

Number of individual labels	250
Printing	pre-printed

Dimensions

Width	280.00 mm
Height	26.00 mm
Depth	0.08 mm

Material specifications

Foil strength	50 µm
Adhesive strength	24 µm
Adhesive	Acrylic
Color	blue (RAL 5015)
Base element material	Polyester

Environmental and real-life conditions

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
---------------	--------------------------------------

PML-T110 (26X280)R - Pipeline marker



1014247

<https://www.phoenixcontact.com/us/products/1014247>

	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 7 °C
Recommended ambient temperature (storage/transport)	20 °C ... 25 °C
Recommended humidity (storage/transport)	40 % ... 50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Mounting

Mounting type	adhesive
---------------	----------

PML-T110 (26X280)R - Pipeline marker



1014247

<https://www.phoenixcontact.com/us/products/1014247>

Classifications

ECLASS

ECLASS-13.0	40200202
ECLASS-15.0	40200202

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

PML-T110 (26X280)R - Pipeline marker



1014247
<https://www.phoenixcontact.com/us/products/1014247>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com