

# PSR-M-TBUS2-SC - Extension module



1105097

<https://www.phoenixcontact.com/us/products/1105097>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safe extension module for local bus extension, 2 function channels, TBUS interface, up to SIL 3, Cat. 4/PL e, plug-in screw terminal block, TBUS connector included

## Product description

The configurable and individually scalable PSRmodular safety system is a flexible safety solution for monitoring your machine or system. The extension module is for extending the local bus in the PSRmodular system. Therefore, additional extension modules can be integrated into the system that are at a certain distance from the base station.

## Your advantages

- Cost-effective safety solution with a high level of adaptability to individual requirements
- Fast startup, thanks to easy hardware and software configuration
- Machine downtimes minimized with comprehensive, easy-to-understand diagnostics
- Low housing width of just 22.6 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1105097       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN02          |
| Product key                          | DNA362        |
| GTIN                                 | 4055626974828 |
| Weight per piece (including packing) | 171 g         |
| Weight per piece (excluding packing) | 138 g         |
| Customs tariff number                | 85371098      |
| Country of origin                    | IT            |

# PSR-M-TBUS2-SC - Extension module

1105097

<https://www.phoenixcontact.com/us/products/1105097>



## Technical data

### Notes

Note on application

Note on application

Only for industrial use

### Product properties

|              |                     |
|--------------|---------------------|
| Product type | Extension module    |
| Application  | Local bus extension |

#### Insulation characteristics

|                  |     |
|------------------|-----|
| Protection class | III |
|------------------|-----|

#### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 2  |

### Electrical properties

|   |   |
|---|---|
| Maximum power dissipation for nominal condition | 0.8 W   |
| Nominal operating mode                          | 100% operating factor   |
| Interfaces                                      | DIN rail TBUS for connection to the master module, supplied as standard |
| Rated surge voltage/insulation                  | Basic insulation 4 kV between all current paths and housing             |

#### Brake to be connected

|                   |                  |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

#### Supply

|  |  |
|--|--|
| Designation                                | A1/A2  |
| Rated control circuit supply voltage $U_S$ | 19.2 V DC ... 28.8 V DC  |
| Rated control circuit supply voltage $U_S$ | 24 V DC -20 % / +20 % (provide external protection, typically 1 A) |
| Rated control supply current $I_S$         | typ. 33 mA (at $U_S$ )   |
| Power consumption at $U_S$                 | typ. 0.8 W   |
| Inrush current                             | max. 8 A ( $\Delta t = 200 \mu s$ at $U_S$ )                       |
| Filter time                                | typ. 20 ms (in the event of voltage dips at $U_S$ )                |
| Protective circuit                         | Serial protection against polarity reversal                        |
|  | Varistor   |

### Connection data

|                   |                  |
|-------------------|------------------|
| Connection method | Screw connection |
| Stripping length  | 7 mm             |
| Tightening torque | 0.5 ... 0.6 Nm   |
| Screw thread      | M3               |

### Interfaces

# PSR-M-TBUS2-SC - Extension module

1105097

<https://www.phoenixcontact.com/us/products/1105097>



## Data: Local bus extension

|                        |  |
|------------------------|--|
| Communication protocol | RS-485   |
| Connection method      | Terminal block   |
| Number of connections  | 2  |
| Note                   | Note the requirements for the transmission cable in accordance with the data sheet section "Wiring". |

## Signaling

|                           |                 |
|---------------------------|-----------------|
| Status display            | 1 x LED (green) |
| Operating voltage display | 1 x LED (green) |
| Error indication          | 2 x LED (red)   |

## Dimensions

|        |           |
|--------|-----------|
| Width  | 22.61 mm  |
| Height | 112.58 mm |
| Depth  | 113.6 mm  |

## Material specifications

|                  |                             |
|------------------|-----------------------------|
| Color (Housing)  | yellow (RAL 1018)           |
| Housing material | Polyamide PA non-reinforced |

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Degree of protection                           | IP20   |
| Min. degree of protection of inst. location    | IP54   |
| Ambient temperature (operation)                | -10 °C ... 55 °C (observe derating)  |
| Ambient temperature (storage/transport)        | -20 °C ... 85 °C   |
| Maximum altitude                               | ≤ 2000 m (Above sea level)   |
| Max. permissible humidity (storage/transport)  | 95 % (non-condensing)  |
| Max. permissible relative humidity (operation) | 95 % (non-condensing)  |
| Shock  | 10g for $\Delta t = 16$ ms (continuous shock, 1000 shocks in each space direction) |
| Vibration (operation)                          | 10 Hz ... 150 Hz, 2g   |

## Approvals

|                |              |
|----------------|--------------|
| CE             |              |
| Identification | CE-compliant |

## Mounting

|                   |                        |
|-------------------|------------------------|
| Mounting type     | DIN rail mounting      |
| Mounting position | vertical or horizontal |


# PSR-M-TBUS2-SC - Extension module



1105097

<https://www.phoenixcontact.com/us/products/1105097>

## Drawings



Block diagram

# PSR-M-TBUS2-SC - Extension module



1105097

<https://www.phoenixcontact.com/us/products/1105097>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1105097>



**cULus Listed**

Approval ID: E238705



**Functional Safety**

Approval ID: Z10029429 0013Rev.02

# PSR-M-TBUS2-SC - Extension module

1105097

<https://www.phoenixcontact.com/us/products/1105097>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371819 |
| ECLASS-15.0 | 27371819 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001449 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122200 |
|-------------|----------|

# PSR-M-TBUS2-SC - Extension module

1105097

<https://www.phoenixcontact.com/us/products/1105097>



## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)