

1337238  
<https://www.phoenixcontact.com/us/products/1337238>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular RJ45 PCB connectors, 1x1 single-port, connection direction of the connector to the PCB: 180 °, Shielded, number of positions: 8, 10 Gbps, PoE++, THT-THR, Reflow, type of packaging: Tape and Reel

Your advantages

- The right version for every application. Available with and without LED, single- and multi-port
- The reflow capability enables efficient, cost-optimized processing
- High standoffs allow ideal thermal airflow during processing
- Tape-on-reel packaging is perfect for automated processing
- The extended temperature range from -50 °C ... +85 °C enables use in demanding applications
- Through-hole technology (THT) provides high mechanical stability when connecting the female connector to the PCB

Commercial data

Item number	1337238
Packing unit	120 pc
Minimum order quantity	120 pc
Sales key	AB12
Product key	ABNADA
GTIN	4063151638436
Weight per piece (including packing)	7.41 g
Weight per piece (excluding packing)	7.34 g
Customs tariff number	85366930
Country of origin	CN

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Technical data

### Product properties

Product type	Data connector (device side)
Slots	1x1 single-port
Orientation to PCB	180.00 °
Type	THD
Number of positions	8 (8P8C)
Type of locking	Snap-in locking
Shielding	Shielded
application range	Reflow
Type of packaging	Tape and Reel
Transmission speed	10 Gbps
PoE/PoE+	PoE++
Power PSE	90 W (Class 8 in accordance with IEEE 802.3bt)
Power PD	71 W (Class 4 in accordance with IEEE 802.3bt)

### Electrical properties

Rated voltage	72 V DC
Rated surge voltage	1.5 kV DC (IEC 60664-1)
Rated current	1.5 A (IEC 60603-7)
Frequency range	10 Hz ... 500 Hz
Test voltage	1.5 kV DC IEC 60603-7 (Contact - contact)
	1.5 kV DC IEC 60603-7 (Contact - shield)
Insulation resistance	> 500 MΩ (IEC 60603-7)
Transmission speed	10 Gbps
Transmission speed	10 Gbps
Power transmission	PoE++

### Connection data

#### Connection technology

Connection method	Female
-------------------	--------

### Signaling

Status display present	no
------------------------	----

### Dimensions

Width	16.8 mm
Height	13.6 mm
Length	19 mm
Installed height	15.90 mm
Orientation to PCB	180.00 °
Data pin length	2.00 mm

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Material specifications

Material Plug contact coating (top layer/selective)	Au (1.27 µm/50 µ")
Material Plug contact coating (intermediate layer)	Ni (1.27 µm/50 µ")
Material Solder contact coating (top layer/selective)	Sn (2.54 µm / 100 µ")
Material Solder contact coating (intermediate layer)	Ni (1.27 µm/50 µ")
Material Contact	Phosphor bronze
Material Housing pin coating (top layer/selective)	Sn
Material Contact carrier	LCP (Housing (female/insert))

## Cable/line

Shielding	Shielded
Halogen-free	yes
Flame resistance	UL 94 V0

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 750 (IEC 60603-7)
Insertion force	< 20 N (IEC 60603-7)
Withdrawal force	< 20 N (IEC 60603-7)

## Environmental and real-life conditions

### Test specification

Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s <sup>2</sup>
Test duration	20.00 s

### Test specification

Specification	IEC60068-2-27
Acceleration	295.00 m/s <sup>2</sup>

### Ambient conditions

Degree of protection (when plugged in)	IP20 (IEC 60603-7)
Degree of protection (not plugged in)	IP20 (IEC 60603-7)
Ambient temperature (operation)	-50 °C ... 85 °C
Ambient temperature (storage/transport)	-50 °C ... 85 °C

## Standards and regulations

Flame resistance	UL 94 V0
------------------	----------

## Mounting

Mounting type	THT-THR
---------------	---------

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Processing notes

Process	THR
Moisture Sensitive Level	MSL 1
Classification temperature T <sub>c</sub>	260 °C
Solder cycles in the reflow	3

## Packaging specifications

Type of packaging	Tape and Reel
[W] tape width	44 mm
[W2] coil overall dimension	49.1 mm
[A] coil diameter	330 mm

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors




1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Drawings

Diagram



Classification reflow soldering profile

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1337238>



**UL Recognized**

Approval ID: FILE E 335024

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238  
<https://www.phoenixcontact.com/us/products/1337238>

## Classifications

### ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

### ETIM

ETIM 9.0	EC002637
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238  
<https://www.phoenixcontact.com/us/products/1337238>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)