

# NBC-M12MSD/ 2,0-93B/M12FSD - Network cable



1407554

<https://www.phoenixcontact.com/us/products/1407554>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, PROFINET CAT5 (100 Mbps), EtherCAT® CAT5 (100 Mbps), 4-position, PVC/PVC, green RAL 6018, shielded (Advanced Shielding Technology), Plug straight M12, coding: D / IP67, on Socket straight M12 / IP67, cable length: 2 m

## Commercial data

Item number	1407554
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF04
Product key	AF1CJN
GTIN	4046356778589
Weight per piece (including packing)	156 g
Weight per piece (excluding packing)	138.778 g
Customs tariff number	85444210
Country of origin	PL

## Technical data

### Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 10.1 Cord Sets for Balanced Cabling
General	Further products with variable cable type and variable cable length can be found in the accessories section

### Product properties

Product type	Data cable preassembled
Application	Standard
Sensor type	PROFINET
Number of positions	4
Shielded	yes

### Interfaces


Signal type/category	PROFINET CAT5 (IEC 11801), 100 Mbps
	EtherCAT® CAT5 (IEC 11801), 100 Mbps

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	4 A
Transmission medium	Copper
Transmission speed	100 Mbps

### Connector

#### Connection 1


Dimensional drawing	 Pin assignment M12 male connector, 4-pos., D-coded, male side
Type	M12 Plug, straight, 4-position, shielded (Advanced Shielding Technology), Keying: D
Number of positions	4
Shielded	yes
Shielding	Advanced Shielding Technology
Signal type/category	EtherCAT® CAT5 (IEC 11801), 100 Mbps PROFINET CAT5 (IEC 11801)
Insertion/withdrawal cycles	≥ 100

1407554

<https://www.phoenixcontact.com/us/products/1407554>

Insulation resistance	≥ 100 MΩ
Overvoltage category	II
Degree of pollution	3
Tightening torque	0.4 Nm
Material Contact	CuSn
Material Contact surface	Ni/Au
Material Contact carrier	PA 6.6
Material Screw connection	Die-cast zinc, nickel-plated
Material Grip body	TPU, hardly inflammable, self-extinguishing
Material Seal	FKM
Flammability rating according to UL 94	V0
Degree of protection	IP65 IP67
Ambient temperature (operation)	-25 °C ... 85 °C
Standard designation	M12 connector
Standards/regulations	IEC 61076-2-101

## Connection 2

Dimensional drawing	 <p>Pin assignment M12 socket, 4-pos., D-coded, female side</p>
Type	M12 Socket, straight, 4-position, shielded (Advanced Shielding Technology), Keying: D
Number of positions	4
Shielded	yes
Shielding	Advanced Shielding Technology
Signal type/category	EtherCAT® CAT5 (IEC 11801), 100 Mbps PROFINET CAT5 (IEC 11801)
Insertion/withdrawal cycles	≥ 100
Insulation resistance	≥ 100 MΩ
Overvoltage category	II
Degree of pollution	3
Tightening torque	0.4 Nm
Material Contact	CuSn
Material Contact surface	Ni/Au
Material Contact carrier	PA 6.6
Material Screw connection	Die-cast zinc, nickel-plated
Material Grip body	TPU, hardly inflammable, self-extinguishing
Material Seal	FKM
Flammability rating according to UL 94	V0
Degree of protection	IP65

# NBC-M12MSD/ 2,0-93B/M12FSD - Network cable



1407554


<https://www.phoenixcontact.com/us/products/1407554>

	IP67
Ambient temperature (operation)	-25 °C ... 85 °C
Standard designation	M12 connector
Standards/regulations	IEC 61076-2-101

## Cable/line

Cable length	2 m
--------------	-----

### PROFINET PVC stranded CAT5 [93B]

Dimensional drawing		
UL AWM Style	21695 (80 °C / 600 V)	
Number of positions	4	
Shielded	yes	
Cable type	PROFINET PVC stranded CAT5 [93B]	
Conductor structure	1x4xAWG22/7, SF/TQ	
AWG signal line	22	
Conductor cross section	4x 0.34 mm <sup>2</sup>	
Wire diameter incl. insulation	1.5 mm ±0.1 mm	
External cable diameter	6.50 mm ±0.2 mm	
Outer sheath, material	PVC	
External sheath, color	green RAL 6018	
Conductor material	Tin-plated Cu litz wires	
Material wire insulation	PE	
Single wire, color	white, yellow, blue, orange	
Overall twist	Star quad	
Optical shield covering	85 %	
Insulation resistance	≥ 5 GΩ*km	
Loop resistance	≤ 120.00 Ω/km	
Wave impedance	100 Ω ±5 Ω (at 100 MHz)	
Nominal voltage, cable	≤ 600 V	
Test voltage Core/Core	2000 V ((50 Hz/1 min))	
Test voltage Core/Shield	2000.00 V ((50 Hz/1 min))	
Minimum bending radius, fixed installation	4 x D	
Minimum bending radius, flexible installation	8 x D	
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1) UL 1685 (CSA FT 4) UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)	

# NBC-M12MSD/ 2,0-93B/M12FSD - Network cable



1407554

<https://www.phoenixcontact.com/us/products/1407554>

Resistance to oil	OIL RES I according to UL 2256
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-10 °C ... 70 °C (Cable, flexible installation)


## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight, shielded

1407554


<https://www.phoenixcontact.com/us/products/1407554>

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

Schematic diagram




Pin assignment M12 socket, 4-pos., D-coded, female side

1407554

<https://www.phoenixcontact.com/us/products/1407554>

Circuit diagram



Contact assignment of the M12 connector and the M12 socket



# NBC-M12MSD/ 2,0-93B/M12FSD - Network cable





1407554


<https://www.phoenixcontact.com/us/products/1407554>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1407554>

<div><b>UL Listed</b> Approval ID: FILE E 335024</div>				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	250 V	4 A	-	-

<div><b>cUL Listed</b> Approval ID: FILE E 335024</div>				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	250 V	4 A	-	-

<div><b>EAC-RoHS</b> Approval ID: RU D-DE.HB35.B.00387</div>				
---	--	--	--	--

1407554

<https://www.phoenixcontact.com/us/products/1407554>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%