

# SAC-3P-10,0-547/MINFS - Power cable



1416552

<https://www.phoenixcontact.com/us/products/1416552>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 3-position, PVC, yellow, free cable end, on Socket straight 7/8"-16UNF, coding: A, cable length: 10 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1416552                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF14                           |
| Product key                          | AF1IMA                         |
| GTIN                                 | 4055626221342                  |
| Weight per piece (including packing) | 22.22 g                        |
| Weight per piece (excluding packing) | 22.22 g                        |
| Customs tariff number                | 85444290                       |
| Country of origin                    | MX                             |

# SAC-3P-10,0-547/MINFS - Power cable



1416552

<https://www.phoenixcontact.com/us/products/1416552>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 3                     |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Material specifications

|                                        |                   |
|----------------------------------------|-------------------|
| Flammability rating according to UL 94 | V0                |
| Material of grip body                  | PVC               |
| Contact material                       | CuZn              |
| Contact surface material               | Au                |
| Contact carrier material               | PVC               |
| Material for screw connection          | Anodized aluminum |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 300 V AC/DC (UL rating)    |
|                       | 50 V AC/DC (IEC rating)    |
| Nominal current $I_N$ | 13 A                       |

### Mechanical properties

#### Mechanical data

|                             |     |
|-----------------------------|-----|
| Insertion/withdrawal cycles | 100 |
|-----------------------------|-----|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |                         |
|-------------------|-------------------------|
| Tightening torque | 10 lb <sub>F</sub> ·in. |
|                   | 1.12 Nm                 |

### Connector

#### Connection 1

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

#### Connection 2

|      |                            |
|------|----------------------------|
| Type | Socket straight 7/8"-16UNF |
|------|----------------------------|

# SAC-3P-10,0-547/MINFS - Power cable



1416552


<https://www.phoenixcontact.com/us/products/1416552>

|                     |   |
|---------------------|---|
| Number of positions | 3 |
| Coding type         | A |

## Cable/line

|              |      |
|--------------|------|
| Cable length | 10 m |
|--------------|------|

PVC AWG 18 yellow 105°C [547]

|                                             |                                                                                    |
|---------------------------------------------|------------------------------------------------------------------------------------|
| Dimensional drawing                         |  |
| UL AWM Style                                | 2517 (105 °C / 300 V)                                                              |
| Number of positions                         | 3                                                                                  |
| Shielded                                    | no                                                                                 |
| Cable type                                  | PVC AWG 18 yellow 105°C [547]                                                      |
| Conductor structure signal line             | 41x 0.16 mm                                                                        |
| AWG signal line                             | 18                                                                                 |
| Wire diameter incl. insulation              | 1.7 mm ±0.03 mm                                                                    |
| External cable diameter                     | 5.70 mm ±0.2 mm                                                                    |
| Outer sheath, material                      | PVC                                                                                |
| External sheath, color                      | yellow                                                                             |
| Conductor material                          | Tin-plated Cu litz wires                                                           |
| Material wire insulation                    | PVC                                                                                |
| Single wire, color                          | brown, blue, black                                                                 |
| Overall twist                               | 3 wires, twisted                                                                   |
| Nominal voltage, cable                      | 300 V                                                                              |
| Minimum bending radius, fixed installation  | 8 x D                                                                              |
| Smallest bending radius, fixed installation | 46 mm                                                                              |
| Flame resistance                            | FT4                                                                                |
| Special properties                          | UL ITC/PLTC 105 °C<br>CSA AWM I/II A/B FT4 105 °C / 300 V                          |
| Ambient temperature (operation)             | -30 °C ... 105 °C (cable, fixed installation)                                      |

## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                               |
|-------------------------------------------------------------------|-----------------------------------------------|
| Degree of protection                                              | IP68                                          |
| Ambient temperature (operation) (male connector/female connector) | -20 °C ... 105 °C (Plug / socket)             |
| Ambient temperature (operation)                                   | -20 °C ... 105 °C (Plug / socket)             |
| Ambient temperature (operation) (Cable, fixed installation)       | -40 °C ... 105 °C (cable, fixed installation) |

# SAC-3P-10,0-547/MINFS - Power cable



1416552

<https://www.phoenixcontact.com/us/products/1416552>

|                                                                |
|----------------------------------------------------------------|
| Ambient temperature (operation) (Cable, flexible installation) |
|----------------------------------------------------------------|

|                                                  |
|--------------------------------------------------|
| -30 °C ... 105 °C (Cable, flexible installation) |
|--------------------------------------------------|

# SAC-3P-10,0-547/MINFS - Power cable




1416552

<https://www.phoenixcontact.com/us/products/1416552>


## Drawings

Dimensional drawing



7/8"-16UNF socket, straight

Schematic diagram



Pin assignment, socket, 7/8"-16UNF, 3-pos., view of female side


# SAC-3P-10,0-547/MINFS - Power cable



1416552

<https://www.phoenixcontact.com/us/products/1416552>

Circuit diagram



Contact assignment of 7/8" socket

# SAC-3P-10,0-547/MINFS - Power cable



1416552

<https://www.phoenixcontact.com/us/products/1416552>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1416552>



**UL Listed**

Approval ID: FILE E 221474



**cUL Listed**

Approval ID: FILE E 221474

# SAC-3P-10,0-547/MINFS - Power cable



1416552

<https://www.phoenixcontact.com/us/products/1416552>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31251501 |
|-------------|----------|

# SAC-3P-10,0-547/MINFS - Power cable



1416552

<https://www.phoenixcontact.com/us/products/1416552>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)