

SACC-DSI-MS-8P-M12/0,5 0,14SCO - Panel feed-through



1444089

<https://www.phoenixcontact.com/us/products/1444089>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator flush-type plug, 8-pos., M12 SPEEDCON, rear/screw mounting with M12 thread, with 0.5 m TPE litz wire, 8 x 0.25 mm²

Commercial data

Item number	1444089
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	ABQCGA
GTIN	4046356525534
Weight per piece (including packing)	18.8 g
Weight per piece (excluding packing)	18.8 g
Country of origin	DE

SACC-DSI-MS-8P-M12/0,5 0,14SCO - Panel feed-through



1444089

<https://www.phoenixcontact.com/us/products/1444089>

Technical data

Product properties

Number of positions	8
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V
Nominal current I_N	2 A
Max. conductor resistance	80 m Ω /m

Connection data

Connection method	Individual wires
-------------------	------------------

Signaling

Status display	no
Status display present	no

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated
Conductor material	Tin-plated Cu litz wires

Cable/line

Cable length	0.5 m
Cable type	TPE litz wire
Single wire, color	brown, blue, white, gray, pink, green, yellow, red
Cable cross section	0.14 mm ²
Conductor material	Tin-plated Cu litz wires
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Material wire insulation	TPE

SACC-DSI-MS-8P-M12/0,5 0,14SCO - Panel feed-through



1444089

<https://www.phoenixcontact.com/us/products/1444089>

Thickness, insulation	0.21 mm
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Cable resistance	≤ 80 mΩ/m
Cable insulation resistance	≥ 20 MΩ*km

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-25 °C ... 90 °C (cable, fixed installation)


SACC-DSI-MS-8P-M12/0,5 0,14SCO - Panel feed-through

1444089

<https://www.phoenixcontact.com/us/products/1444089>


Drawings

Dimensional drawing



M12 flush-type connector

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side


SACC-DSI-MS-8P-M12/0,5 0,14SCO - Panel feed-through



1444089

<https://www.phoenixcontact.com/us/products/1444089>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com