

# PATG HF 3/12 - Conductor marker carrier



1014057

<https://www.phoenixcontact.com/us/products/1014057>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, transparent/black, unlabeled, cable diameter range: 4 ... 7 mm, mounting type: slide-on, text field height: 4 mm, text field width: 12 mm

## Your advantages

- The PATG HF... sleeve is a captive marker carrier
- These conductor marking systems consist of marker carriers and insert labels
- Comprehensive approvals ensure international use
- The use of high-quality plastics supports the most stringent demands of the rail industry and the automotive industry
- The corresponding UCT-WMT... and UC-WMT... insert labels are used for marking
- Due to the plastic properties of the PATG HF..., high-quality fluid printing of the UC-WMT... with the BLUEMARK... is required

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1014057       |
| Packing unit                         | 500 pc        |
| Minimum order quantity               | 500 pc        |
| Sales key                            | BG12          |
| Product key                          | BG221A        |
| GTIN                                 | 4046356779449 |
| Weight per piece (including packing) | 0.318 g       |
| Weight per piece (excluding packing) | 22.22 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

## Technical data

### Product properties

|              |                      |
|--------------|----------------------|
| Product type | Marker carrier cable |
| Type         | Profile              |

### Dimensions

|        |        |
|--------|--------|
| Width  | 12 mm  |
| Height | 8.9 mm |
| Depth  | 9.1 mm |

### External dimensions

|                  |               |
|------------------|---------------|
| Outside diameter | 4 mm ... 7 mm |
|------------------|---------------|

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 12 mm |
| Text field height | 4 mm  |

### Material specifications

|                                                        |                                          |
|--------------------------------------------------------|------------------------------------------|
| Color                                                  | multicolored                             |
|                                                        | transparent                              |
|                                                        | black (RAL 9005)                         |
| Material                                               | TPU                                      |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2                              |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3                              |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3                              |
| Components                                             | free from silicone, halogen, and cadmium |

### Cable/line

|                         |               |
|-------------------------|---------------|
| External cable diameter | 4 mm ... 7 mm |
|-------------------------|---------------|

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                    |
|---------------|--------------------|
| Specification | ISO 4892-2:2013-03 |
| Result        | Test passed        |
| Test duration | 96 h               |

#### Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 100 °C (121 °C) | Test passed                     |
| Specification          | ISO 175:2010 (following)        |

# PATG HF 3/12 - Conductor marker carrier



1014057

<https://www.phoenixcontact.com/us/products/1014057>

|                                                   |             |
|---------------------------------------------------|-------------|
| Test duration                                     | 168 h       |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed |
| IRM 901                                           | Test passed |
| IRM 902                                           | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

Ambient conditions

|                                                     |                                                                                                         |
|-----------------------------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 85 °C                                                                                        |
| Recommended storage conditions                      | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                                                   |
| Recommended humidity (storage/transport)            | 50 %                                                                                                    |
| Shelf life                                          | 2 years                                                                                                 |

## Standards and regulations

Standards

|                       |            |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

# PATG HF 3/12 - Conductor marker carrier



1014057

<https://www.phoenixcontact.com/us/products/1014057>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002248 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PATG HF 3/12 - Conductor marker carrier



1014057  
<https://www.phoenixcontact.com/us/products/1014057>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |
| EF3.0 Climate Change                    |                            |
| CO2e kg                                 | 0.008 kg CO2e              |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)