

RF-12F1N8A80DU - Cable connector



1616138

<https://www.phoenixcontact.com/us/products/1616138>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, straight, M23, number of positions: 12, contact connection type: Socket, shielded: yes, cable diameter range: 3 mm ... 13.2 mm, number of positions: 12, connection method: Crimp connection, series: RF

Commercial data

Item number	1616138
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAGA
GTIN	4046356516358
Weight per piece (including packing)	100.24 g
Weight per piece (excluding packing)	95.23 g
Country of origin	DE

RF-12F1N8A80DU - Cable connector



1616138

<https://www.phoenixcontact.com/us/products/1616138>

Technical data

Notes

Order information:

Order crimp contacts Ø 1 mm separately

Product properties

Series	RF
Application	Feedback, signal
	Signal
Number of positions	12
Connection profile	12
Shielded	yes
Coding	N
Pg screw connection	none

Electrical properties

Contact

Nominal current I_N	8 A
Nominal voltage U_N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Crimp connection
-------------------	------------------

Material specifications

Seal material	FPM
---------------	-----

Connector

Type	straight
Direction of rotation	Standard

Cable/line

External cable diameter	3 mm ... 13.2 mm
-------------------------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

RF-12F1N8A80DU - Cable connector


1616138

<https://www.phoenixcontact.com/us/products/1616138>



Drawings

Dimensional drawing



RF-12F1N8A80DU - Cable connector



1616138

<https://www.phoenixcontact.com/us/products/1616138>

Classifications

UNSPSC

UNSPSC 21.0	39121419
-------------	----------

RF-12F1N8A80DU - Cable connector



1616138

<https://www.phoenixcontact.com/us/products/1616138>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com