

VS-15-A-EMV-S - Panel-mount frame



1688049

<https://www.phoenixcontact.com/us/products/1688049>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB EMC shroud, shell size 2, shielded, for panel mounting frame VS-15-...



Commercial data

Item number	1688049
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCBZ
GTIN	4017918182311
Weight per piece (including packing)	0.844 g
Weight per piece (excluding packing)	0.8 g
Customs tariff number	85389099
Country of origin	DE

VS-15-A-EMV-S - Panel-mount frame



1688049

<https://www.phoenixcontact.com/us/products/1688049>

Technical data

Product properties

Product type	Panel-mount frame
Application	Shroud
Type	Shell size 2
Connection profile	D-SUB

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties

Transmission medium	Copper
---------------------	--------

Dimensions

Width	0.6 mm
Height	44.3 mm
Length	17.5 mm

Material specifications

Color	Bare metallic
Material	Metal
Housing material	Metal
Housing surface material	nickel-plated

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 1000
-----------------------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 80 °C

Mounting

Mounting type	Front mounting
---------------	----------------

VS-15-A-EMV-S - Panel-mount frame



1688049

<https://www.phoenixcontact.com/us/products/1688049>

Classifications

ECLASS

ECLASS-13.0	27440210
ECLASS-15.0	27440210

ETIM

ETIM 9.0	EC002310
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

VS-15-A-EMV-S - Panel-mount frame



1688049

<https://www.phoenixcontact.com/us/products/1688049>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com