

FQ 2,54D/ 30-PH-1-BT - Pin strip

1156943

<https://www.phoenixcontact.com/us/products/1156943>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

SMD pin header, nominal current: 3 A, test voltage: 500 V AC, number of positions: 30, pitch: 2.54 mm, color: black, contact surface: Au, contact connection type: Pin, mounting: SMD soldering



Your advantages

- Reliable mechanical and electrical connections thanks to the double-sided contact system
- Designed for integration into the SMT soldering process
- Clear and cost-optimized design
- Suitable for a multitude of applications
- Stacked, coplanar or orthogonal PCB connections enable maximum flexibility in the device

Commercial data

Item number	1156943
Packing unit	130 pc
Minimum order quantity	130 pc
Sales key	AA24
Product key	AAXGBA
GTIN	4063151160340
Weight per piece (including packing)	3.446 g
Weight per piece (excluding packing)	3 g
Customs tariff number	85366930
Country of origin	CN

FQ 2,54D/ 30-PH-1-BT - Pin strip



1156943

<https://www.phoenixcontact.com/us/products/1156943>

Technical data

Notes

Notes on operation	The permissible voltage during operation depends on the application, taking into consideration the air clearances and creepage distances within the scope of insulation requirements in accordance with IEC 60664-1.
--------------------	--

Product properties


Product type	SMD pin header
Product family	FQ 2,54D/...-PH
Number of positions	30
Pitch	2.54 mm
Number of rows	2
Pin layout	Linear pad geometry

Electrical properties

Properties

Nominal current I_N	3 A (at 20°C 80-pos.)
Contact resistance	20 mΩ
Test voltage	500 V AC IEC 60512-4-1:2003-05

Dimensions

Dimensional drawing	
Pitch	2.54 mm
Width [w]	38.1 mm
Height [h]	6.28 mm
Length [l]	16.1 mm
Installed height	5.08 mm

Application

Contact cover	0.4 mm
Wipe length	1.3 mm

PCB design

Pad geometry	1.3 x 2.8 mm
--------------	--------------

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC
------	--

FQ 2,54D/ 30-PH-1-BT - Pin strip



1156943

<https://www.phoenixcontact.com/us/products/1156943>

	60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	Selective coating
Metal surface contact area (top layer)	Gold (Au)
Metal surface contact area (middle layer)	Nickel (Ni)
Metal surface soldering area (top layer)	Tin (Sn)

Material data - housing

Color (Housing)	black (9005)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0

Connector

Connection 1

Insulating material	PA
CTI according to IEC 60112	600

Electrical tests

Thermal test | Test group C

Specification	IEC 60512-5-2:2002-02
Tested number of positions	80

Insulation resistance

Specification	IEC 60512-3-1:2002-02
Insulation resistance, neighboring positions	> 1 GΩ

Air clearances and creepage distances |

Insulating material group	I
Minimum value for clearance and creepage distance	0.4 mm

Mechanical tests

Insertion and withdrawal forces

Result	Test passed
No. of cycles	100
Insertion strength per pos. approx.	2.9 N
Withdraw strength per pos. approx.	2.9 N

Visual inspection

Specification	IEC 60512-1-1:2002-02
Result	Test passed

Dimension check

Specification	IEC 60512-1-2:2002-02
---------------	-----------------------

FQ 2,54D/ 30-PH-1-BT - Pin strip

1156943

<https://www.phoenixcontact.com/us/products/1156943>



Result	Test passed
--------	-------------

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 55 - 10 Hz
Sweep speed	1 octave/min
Amplitude	1.52 mm
Acceleration	181 m/s ²
Test duration per axis	2 h
Test directions	X-, Y- and Z-axis

Durability test

Specification	IEC 60512-9-1:2010-03 (following)
Contact resistance R ₁	20 mΩ
Contact resistance R ₂	30 mΩ
Insertion/withdrawal cycles	100
Insulation resistance, neighboring positions	> 1 GΩ

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

Mounting

Mounting type	SMD soldering
Pin layout	Linear pad geometry

Processing notes


Process	Reflow soldering
Moisture Sensitive Level	MSL 1
Classification temperature T _c	260 °C

Packaging specifications

Type of packaging	Tube magazine
-------------------	---------------

Drawings

Diagram



Type: FQ 2,54D/...-SH-O-BT with FQ 2,54D/...-PH-1-BT

FQ 2,54D/ 30-PH-1-BT - Pin strip



1156943

<https://www.phoenixcontact.com/us/products/1156943>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1156943>

	cULus Recognized Approval ID: E118976			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	3 A	-	-

FQ 2,54D/ 30-PH-1-BT - Pin strip

1156943

<https://www.phoenixcontact.com/us/products/1156943>



Classifications

ECLASS

ECLASS-13.0	27460201
-------------	----------

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FQ 2,54D/ 30-PH-1-BT - Pin strip

1156943

<https://www.phoenixcontact.com/us/products/1156943>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com