

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237

<https://www.phoenixcontact.com/us/products/1424237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 8-position, Socket, straight, M8, A-coding, Solder pins

## Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- Standard pin assignments and codings for signal transmission with a uniform design-in design
- For high transmission reliability: optional shield connection to the housing and latching on the PCB

## Commercial data

Item number	1424237
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB22
Product key	ABQJAG
GTIN	4046356712491
Weight per piece (including packing)	6.575 g
Weight per piece (excluding packing)	6.42 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237

<https://www.phoenixcontact.com/us/products/1424237>

## Technical data

### Mounting

Mounting type	Rear mounting (M10, with flat nut)
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

### Product properties

Product type	Circular connectors (device side)
Number of positions	8
Shielded	no
Coding	A
Thread type	M8

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Contact material	CuSn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

### Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V AC
	30 V DC
Nominal current $I_N$	1.5 A

### Connection data

#### Conductor connection

Connection method	Solder pins
Contact connection type	Socket
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	$\geq 100$
-----------------------------	------------

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237

<https://www.phoenixcontact.com/us/products/1424237>

## Connector

### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	A

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C

## Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting




1424237

<https://www.phoenixcontact.com/us/products/1424237>

## Drawings

Schematic diagram



Connector pin assignment of M8 socket, 8-pos., view of socket side

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting





1424237

<https://www.phoenixcontact.com/us/products/1424237>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424237>

	<b>cUL Recognized</b>			
	Approval ID: E221474-20070307			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	30 V	1.5 A	26	-

	<b>UL Recognized</b>			
	Approval ID: E221474-20070307			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	30 V	1.5 A	26	-

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237

<https://www.phoenixcontact.com/us/products/1424237>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 9.0	EC003568
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSI-M8FS-8CON-M10-L180 - Device connector rear mounting



1424237

<https://www.phoenixcontact.com/us/products/1424237>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a2f18515-48eb-45f8-9a9a-d82dfe7e033d

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)