

SACC-DSIV-FS-4CON-L90 SH SCO - Device connector rear mounting



1439900

<https://www.phoenixcontact.com/us/products/1439900>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Socket, angled, M12-SPEEDCON, coding: A, Rear mounting, M12 x 1, Solder pins, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1439900
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB26
Product key	ABQEHA
GTIN	4046356476638
Weight per piece (including packing)	13.44 g
Weight per piece (excluding packing)	10.275 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-FS-4CON-L90 SH SCO - Device connector rear mounting



1439900

<https://www.phoenixcontact.com/us/products/1439900>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Mounting

Mounting type	Rear mounting M12 x 1 With flat nut
Assembly note	With flat nut

Product properties

Product type	Circular connectors (device side)
Number of positions	4
Shielded	yes
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Solder pins
Contact connection type	Socket

Connector

Connection 1

Head design	Socket
-------------	--------

SACC-DSIV-FS-4CON-L90 SH SCO - Device connector rear mounting



1439900

<https://www.phoenixcontact.com/us/products/1439900>

Head cable outlet	angled
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101


SACC-DSIV-FS-4CON-L90 SH SCO - Device connector rear mounting

1439900

<https://www.phoenixcontact.com/us/products/1439900>

Drawings

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

SACC-DSIV-FS-4CON-L90 SH SCO - Device connector rear mounting




1439900

<https://www.phoenixcontact.com/us/products/1439900>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1439900>

 UL Recognized Approval ID: E118976-20100522	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	250 V	4 A	22	-

SACC-DSIV-FS-4CON-L90 SH SCO - Device connector rear mounting



1439900

<https://www.phoenixcontact.com/us/products/1439900>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-FS-4CON-L90 SH SCO - Device connector rear mounting



1439900

<https://www.phoenixcontact.com/us/products/1439900>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c13267bc-5a0a-40a5-a65c-f05b7cbf5ff8

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com