

# SACC-E-M 8MS-5CON-M 8/0,5 DN - Device connector front mounting



1440119

<https://www.phoenixcontact.com/us/products/1440119>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, DeviceNet™, 5-position, Pin, straight, M8, Front mounting, M8 x 0.5, Individual wires, cable length: 0.5 m, 0.25 mm<sup>2</sup>, PVC litz wire

## Your advantages

- Preassembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness
- Standard pin assignments and codings for signal transmission with a uniform design-in design

## Commercial data

Item number	1440119
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB22
Product key	ABQIAA
GTIN	4046356481328
Weight per piece (including packing)	14.3 g
Weight per piece (excluding packing)	14.2 g
Customs tariff number	85444290
Country of origin	PL

# SACC-E-M 8MS-5CON-M 8/0,5 DN - Device connector front mounting



1440119

<https://www.phoenixcontact.com/us/products/1440119>

## Technical data

### Mounting

Mounting type	Front mounting M8 x 0.5
---------------	-------------------------

### Product properties

Product type	Circular connectors (device side)
Application	Signal
Sensor type	DeviceNet™
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	B
Thread type	M8

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Seal material	Viton
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PUR/PA 6.6
Material for screw connection	Brass, nickel-plated
Conductor material	Tin-plated Cu litz wires

### Electrical properties

Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U <sub>N</sub>	30 V AC
	30 V DC
Nominal current I <sub>N</sub>	4 A

### Connection data

#### Conductor connection

Connection method	Individual wires
Contact connection type	Pin
Conductor cross section	0.25 mm²

### Connector

# SACC-E-M 8MS-5CON-M 8/0,5 DN - Device connector front mounting



1440119

<https://www.phoenixcontact.com/us/products/1440119>

## Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M8

## Cable/line

Cable length	0.5 m
Cable type	PVC litz wire
Signal type/category	DeviceNet™
Single wire, color	gray, red, white, black, blue
Cable cross section	0.25 mm²
Conductor material	Tin-plated Cu litz wires
AWG signal line	26
Material wire insulation	PVC
Ambient temperature (operation)	-40 °C ... 85 °C

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

# SACC-E-M 8MS-5CON-M 8/0,5 DN - Device connector front mounting




1440119

<https://www.phoenixcontact.com/us/products/1440119>

## Drawings

Schematic diagram



Pin assignment M8 plug, 5-pos., B-coded, view plug side

# SACC-E-M 8MS-5CON-M 8/0,5 DN - Device connector front mounting



1440119  
<https://www.phoenixcontact.com/us/products/1440119>

## Classifications

### ECLASS

ECLASS-13.0	27440103
-------------	----------

### ETIM

ETIM 9.0	EC003570
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-E-M 8MS-5CON-M 8/0,5 DN - Device connector front mounting



1440119

<https://www.phoenixcontact.com/us/products/1440119>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e29e772b-1612-487e-a5d3-7c411962faec

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)