

SACC-DSI-M8MS-4CON-L90 SH - Device connector rear mounting



1456048

<https://www.phoenixcontact.com/us/products/1456048>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Pin, angled, M8, coding: A, Rear mounting, M8 x 1, Wave soldering

Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- Standard pin assignments and codings for signal transmission with a uniform design-in design
- For high transmission reliability: optional shield connection to the housing and latching on the PCB

Commercial data

Item number	1456048
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB22
Product key	ABQJAA
GTIN	4046356605915
Weight per piece (including packing)	6.585 g
Weight per piece (excluding packing)	6.585 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-M8MS-4CON-L90 SH - Device connector rear mounting



1456048

<https://www.phoenixcontact.com/us/products/1456048>

Technical data

Mounting

Mounting type	Rear mounting M8 x 1 With flat nut
Assembly note	With flat nut

Product properties

Product type	Circular connectors (device side)
Number of positions	4
Shielded	yes
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Pin
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

Connector

Connection 1

Head design	Pin
-------------	-----

SACC-DSI-M8MS-4CON-L90 SH - Device connector rear mounting



1456048

<https://www.phoenixcontact.com/us/products/1456048>

Head cable outlet	angled
Head thread type	M8
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C
Ambient temperature (operation)	-25 °C ... 85 °C

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104


SACC-DSI-M8MS-4CON-L90 SH - Device connector rear mounting

1456048

<https://www.phoenixcontact.com/us/products/1456048>

Drawings

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

1456048
<https://www.phoenixcontact.com/us/products/1456048>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1456048>

 cUL Recognized Approval ID: E221474-20070307				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	30 V	4 A	24	-

 UL Recognized Approval ID: E221474-20070307				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	30 V	4 A	24	-

SACC-DSI-M8MS-4CON-L90 SH - Device connector rear mounting



1456048
<https://www.phoenixcontact.com/us/products/1456048>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M8MS-4CON-L90 SH - Device connector rear mounting



1456048

<https://www.phoenixcontact.com/us/products/1456048>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	87568659-0b37-41ed-a6b3-644cada1e37b

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com