

# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting



1525636

<https://www.phoenixcontact.com/us/products/1525636>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, CANopen®, DeviceNet™, 5-position, PUR halogen-free, red lilac RAL 4001, shielded, Pin, straight, M12, coding: A, on free cable end, Front mounting, M16 x 1.5, Cable connection, cable length: 1 m, CANopen®/DeviceNet™, PUR, violet, this item is expected to be lead-free from Q1 2027 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Your advantages

- Preassembled with cables in various standard lengths for immediate use
- Customer-specific assemblies and cable lengths can be supplied
- Sealed on the cable side for optimum tightness of seal
- Cable designs for all common networks and fieldbuses
- For high transmission safety: shield connection to the housing with optional EMC nut

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1525636       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB25          |
| Product key                          | ABQDEA        |
| GTIN                                 | 4046356022378 |
| Weight per piece (including packing) | 81.8 g        |
| Weight per piece (excluding packing) | 77.226 g      |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting



1525636

<https://www.phoenixcontact.com/us/products/1525636>

## Technical data

### Notes

|                    |  |
|--------------------|--|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
| Order information: | Lock nut is included in the scope of delivery  |

### Safety note

|             |  |
|-------------|--|
| Safety note | <p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none"><li>• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.</li><li>• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.</li><li>• The products are suitable for applications in plant, controller, and electrical device engineering.</li><li>• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.</li><li>• Assembled products may not be manipulated or improperly opened.</li><li>• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a>).</li><li>• When using the product in direct connection with third-party manufacturers, the user is responsible.</li><li>• For operating voltages &gt; 50 V AC, conductive connector housings must be grounded</li><li>• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.</li><li>• Observe the corresponding technical data. You will find information:<ul style="list-style-type: none"><li>o On the product</li><li>o On the packing label</li><li>o In the supplied documentation</li><li>o Online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> under the product</li></ul></li><li>• Only use tools recommended by Phoenix Contact</li><li>• Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory</li></ul> |
|-------------|--|

# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting



1525636

<https://www.phoenixcontact.com/us/products/1525636>

section of the product at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

## Mounting

|               |   |
|---------------|---|
| Mounting type | Front mounting M16 x 1.5 With locking nut |
| Assembly note | With locking nut                          |

## Product properties

|                      |                                   |
|----------------------|-----------------------------------|
| Product type         | Circular connectors (device side) |
| Sensor type          | CANopen®                          |
| Number of positions  | 5                                 |
| No. of cable outlets | 1                                 |
| Shielded             | yes                               |
| Coding               | A                                 |
| Thread type          | M12                               |

## Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

## Material specifications

|  |                      |
|--|----------------------|
| Flammability rating according to UL 94 | V0                   |
| Seal material                          | NBR                  |
| Contact material                       | CuZn                 |
| Contact surface material               | Ni/Au                |
| Contact carrier material               | PA 6.6               |
| Material for screw connection          | Brass, nickel-plated |
| Outer sheath, material                 | PUR                  |

## Electrical properties

|                                |  |
|--------------------------------|--|
| Rated surge voltage            | 1.5 kV   |
| Contact resistance             | ≤ 3 mΩ   |
| Insulation resistance          | ≥ 100 MΩ   |
| Nominal voltage U <sub>N</sub> | 48 V AC<br>60 V DC   |
| Nominal current I <sub>N</sub> | 4 A (Plug/socket in accordance with IEC 61076-2-101, cable technical data is to be observed) |
| Test voltage                   | 2500 V   |

# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting



1525636

<https://www.phoenixcontact.com/us/products/1525636>

|                     |        |
|---------------------|--------|
| Transmission medium | Copper |
|---------------------|--------|

## Connection data

### Conductor connection

|                         |                                   |
|-------------------------|-----------------------------------|
| Connection method       | Cable connection                  |
| Contact connection type | Pin                               |
| Tightening torque       | 3 Nm ... 4 Nm (Installation-side) |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Pin      |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Coding            | A        |


### Connection 2

|             |                |
|-------------|----------------|
| Head design | free cable end |
|-------------|----------------|

## Cable/line

|              |     |
|--------------|-----|
| Cable length | 1 m |
|--------------|-----|

CANopen®/DeviceNet™, PUR, violet [920]

|                                 |  |
|---------------------------------|--|
| Dimensional drawing             |  |
| Cable weight                    | 90 kg/km   |
| UL AWM Style                    | 21198 (80°C/300 V)   |
| Number of positions             | 4  |
| Shielded                        | yes  |
| Cable type                      | CANopen®/DeviceNet™, PUR, violet [920]   |
| Conductor structure             | 2xAWG24/19+2xAWG22/19  |
| Conductor structure signal line | 19x 0.13 mm  |
| AWG signal line                 | 24   |

# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting



1525636

<https://www.phoenixcontact.com/us/products/1525636>

|   |   |
|---|---|
| Conductor structure, voltage supply           | 19x 0.15 mm   |
| AWG power supply                              | 22  |
| Conductor cross section                       | 2x 0.25 mm <sup>2</sup> (Data cable)  |
|   | 2x 0.34 mm <sup>2</sup> (Power supply)  |
|   | 1x 0.34 mm <sup>2</sup> (Drain wire)  |
| Wire diameter incl. insulation                | 1.95 mm ±0.05 mm (Data cable)   |
|   | 1.4 mm ±0.05 mm (Power supply)  |
| External cable diameter                       | 6.70 mm ±0.3 mm   |
| Outer sheath, material                        | PUR   |
| External sheath, color                        | red lilac RAL 4001  |
| Conductor material                            | Tin-plated Cu litz wires  |
| Material wire insulation                      | Foamed PE (Data cable)  |
|   | PE (Power supply)   |
| Single wire, color                            | red-black, blue-white   |
| Twisted pairs                                 | 2 cores to the pair   |
| Type of pair shielding                        | Plastic-coated aluminum foil, aluminum side outside   |
| Overall twist                                 | 2 pairs around a drain wire in the center to the core   |
| Optical shield covering                       | 80 %  |
| Insulation resistance                         | ≥ 5 GΩ*km (Data cable)  |
|   | ≥ 5 GΩ*km (Power supply)  |
| Loop resistance                               | ≤ 181.80 Ω/km (Data cable)  |
|   | ≤ 114.80 Ω/km (Power supply)  |
| Wave impedance                                | 120 Ω ±10 % (with 1 MHz)  |
| Cable capacity                                | nom. 40 nF/km (Data cable)  |
| Nominal voltage, cable                        | ≤ 300 V (Peak value, not for high-power applications)   |
| Test voltage Core/Core                        | 2000 V (50 Hz, 1 min.)  |
| Test voltage Core/Shield                      | 2000.00 V (50 Hz, 1 min.)   |
| Minimum bending radius, fixed installation    | 5 x D   |
| Minimum bending radius, flexible installation | 10 x D  |
| Smallest bending radius, fixed installation   | 34 mm   |
| Smallest bending radius, movable installation | 67 mm   |
| Dynamic load capacity (bending)               | Max. bending cycles: 5000000, Bending radius: 70 mm, Bending radius: 10 x D, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 3 m/s <sup>2</sup> , Ambient temperature: -20 °C ... 60 °C |
| Shield attenuation                            | ≤ 22.9 dB/km (with 1 MHz)   |
|   | ≤ 16.4 dB/km (At 500 kHz)   |
|   | ≤ 9.5 dB/km (At 125 kHz)  |
| Halogen-free                                  | in accordance with DIN VDE 0472 part 815  |
|   | according to IEC 60754-1  |
| Flame resistance                              | UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)  |
|   | UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)  |
|   | IEC 60332-1-2   |
|   | in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)  |

# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting



1525636

<https://www.phoenixcontact.com/us/products/1525636>

|                                 |   |
|---------------------------------|---|
| Other resistance                | Low adhesion                                      |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)      |
|                                 | -30 °C ... 70 °C (Cable, flexible installation)   |
|                                 | -20 °C ... 60 °C (for installation)               |
|                                 | -20 °C ... 60 °C (cable, drag chain applications) |

## Environmental and real-life conditions

### Ambient conditions

|   |   |
|---|---|
| Degree of protection  | IP67  |
|   | IP65/IP67                                       |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket)                |
|   | -40 °C ... 85 °C (without mechanical actuation) |

## Standards and regulations

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M12 circular connector       |
| Standards/specifications | according to IEC 61076-2-101 |


# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting

1525636

<https://www.phoenixcontact.com/us/products/1525636>


## Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

Circuit diagram



Contact assignment of the M12 plug

# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting



1525636  
<https://www.phoenixcontact.com/us/products/1525636>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1525636>

|  |  |                                |                   |                               |
|--|--|--------------------------------|-------------------|-------------------------------|
|  | <b>cUL Recognized</b><br>Approval ID: E221474-20220907 |                                |                   |                               |
|  | Nominal voltage U <sub>N</sub>                         | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
|  | 30 V   | 1.5 A                          | -                 | -                             |

|  |   |                                |                   |                               |
|--|---|--------------------------------|-------------------|-------------------------------|
|  | <b>UL Recognized</b><br>Approval ID: E221474-20220907 |                                |                   |                               |
|  | Nominal voltage U <sub>N</sub>                        | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
|  | 30 V  | 2 A                            | -                 | -                             |



# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting



1525636  
<https://www.phoenixcontact.com/us/products/1525636>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440103 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC003570 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACCEC-M12MS-5CON-M16/ 1,0-920 - Device connector front mounting



1525636

<https://www.phoenixcontact.com/us/products/1525636>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 0cc2e8a1-8267-44ce-8b75-e7934a0d96f3 |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)