

1530634

https://www.phoenixcontact.com/us/products/1530634

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Pin, straight, M5, coding: A, Rear mounting, M7, Solder pins

Product description

Flush-type connector Rear mounting, one-piece, for wave soldering processes, 180°

Your advantages

• Easy PCB assembly: one-piece connectors for wave soldering

Commercial data

| Item number | 1530634 |
|--------------------------------------|---------------|
| Packing unit | 20 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB21 |
| Product key | ABQNAA |
| GTIN | 4046356024433 |
| Weight per piece (including packing) | 2.825 g |
| Weight per piece (excluding packing) | 2.5 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |



1530634

https://www.phoenixcontact.com/us/products/1530634

Technical data

Mounting

| Mounting type | Rear mounting M7 With locking nut |
|---------------|-----------------------------------|
| Assembly note | With locking nut |

Product properties

| Product type | Circular connectors (device side) |
|---------------------|-----------------------------------|
| Number of positions | 4 |
| Shielded | no |
| Coding | A |
| Thread type | M5 |
| | |

Insulation characteristics

| Overvoltage category | II |
|----------------------|----|
| Degree of pollution | 3 |

Material specifications

| Flammability rating according to UL 94 | НВ |
|--|----------------------|
| Seal material | Viton |
| Contact material | CuZn |
| Contact surface material | Au |
| Contact carrier material | PA 6.6 |
| Material for screw connection | Brass, nickel-plated |

Electrical properties

| Contact resistance | ≤ 3 mΩ |
|--------------------------------|----------|
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U _N | 60 V |
| Nominal current I _N | 1 A |
| Test voltage | 800 V |

Connection data

Conductor connection

| Connection method | Solder pins |
|-------------------------|-------------|
| Contact connection type | Pin |

Connector

Connection 1

| Head design | Pin |
|-------------------|----------|
| Head cable outlet | straight |
| Head thread type | M5 |



1530634

https://www.phoenixcontact.com/us/products/1530634

| Coding | A | |
|---|------------------------------|--|
| Environmental and real-life conditions | | |
| Ambient conditions | | |
| Degree of protection | IP67 | |
| | IP67 | |
| Ambient temperature (operation) (male connector/female connector) | -25 °C 85 °C | |
| Standards and regulations | | |
| Standard designation | M5 connector | |
| Standards/specifications | according to IEC 61076-2-105 | |




1530634

https://www.phoenixcontact.com/us/products/1530634

Drawings

Schematic diagram



Pin assignment M5 plug, 4-pos., view male side



1530634

https://www.phoenixcontact.com/us/products/1530634

Classifications

| ECL | _ASS |
|-----|------|
|-----|------|

| | 20.00 | |
|----|-------------|----------|
| | ECLASS-13.0 | 27440110 |
| E | ГІМ | |
| | ETIM 9.0 | EC003568 |
| UI | NSPSC | |
| | UNSPSC 21.0 | 39121400 |



1530634

https://www.phoenixcontact.com/us/products/1530634

Environmental product compliance

EU RoHS

| Fulfills EU RoHS substance requirements | Yes |
|---|---|
| Exemption | 6(c) |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | f18695a3-b7e9-4c45-8b4d-ddef4d18f04f |

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com