

M23-12S1N8A80DU - Cable connector



1629212

<https://www.phoenixcontact.com/us/products/1629212>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: M23 PRO, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 3 mm ... 15 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Solutions with cross-manufacturer compatibility for standard and fast locking systems
- Reliable under the harshest conditions: cable connectors with vibration brake
- Modern, consistent design for highly convenient operation
- Easy, cost-effective cable assembly: uniform shielding of M17 to M40

Commercial data

Item number	1629212
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB30
Product key	ABRABA
GTIN	4055626618456
Weight per piece (including packing)	118.7 g
Weight per piece (excluding packing)	102.821 g
Customs tariff number	85366990
Country of origin	DE

M23-12S1N8A80DU - Cable connector



1629212

<https://www.phoenixcontact.com/us/products/1629212>

Technical data

Notes

Order information:	Order 12 x 1 mm crimp contacts separately
Safety note	
Safety note	WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property. • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible. • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product. • The products are suitable for applications in plant, controller, and electrical device engineering. • When operating the connectors in outdoor applications, they must be separately protected against environmental influences. • Assembled products may not be manipulated or improperly opened. • Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products). • When using the product in direct connection with third-party manufacturers, the user is responsible. • For operating voltages > 50 V AC, conductive connector housings must be grounded • Ensure that the protective or functional ground has been properly connected. • VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector • Only use tools recommended by Phoenix Contact • The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product. • Operate the connector only when it is fully plugged in and interlocked. • Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards. • Observe the minimum bending radius of the cable. Lay the cable without twisting it. • The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting

M23-12S1N8A80DU - Cable connector



1629212

<https://www.phoenixcontact.com/us/products/1629212>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type

Circular connector (cable-side)

Connector

Connection 1

Head design

Socket

Insulating body

Note

Order information: Order crimp contacts Ø 1 mm separately

Coding

N

Insertion/withdrawal cycles

100

Connection method

Crimp connection

Contact switching type

Socket

Application

Signal

Number of positions

12

Direction of rotation

Standard

Connection profile

12

Number Contact (Signal contacts)

12

Diameter Contact (Signal contacts)

1 mm

Litz wire cross-section min. Contact (Signal contacts)

0.08 mm²

Litz wire cross-section max. Contact (Signal contacts)

1 mm²

Nominal current per signal contact

8 A (for max. connection cross section)

Rated voltage Contact (Signal contacts)

150 V

Rated surge voltage

2.5 kV

Overvoltage category

III

Degree of pollution

3

Installation height

2000 m

Housing

Thread type

M23

Type of locking

Screw locking mechanism

Pg screw connection

none

Housing material

GD-Zn

Degree of protection (plugged in)

IP66/IP68 (2 m / 24 h) IP69K

Seal

External cable diameter

3 mm ... 15 mm (Universal gasket)

Seal material

FKM

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

-40 °C ... 105 °C (see to derating)

Permanent temperature

125 °C (DIN EN 60512-9-2 / 1000 h)

M23-12S1N8A80DU - Cable connector




1629212

<https://www.phoenixcontact.com/us/products/1629212>


Drawings

Dimensional drawing



Dimensional drawing, housing

Dimensional drawing




Dimensional drawing, housing

M23-12S1N8A80DU - Cable connector

1629212

<https://www.phoenixcontact.com/us/products/1629212>

Schematic diagram



Connector pin assignment


M23-12S1N8A80DU - Cable connector

1629212

<https://www.phoenixcontact.com/us/products/1629212>



Schematic diagram




Connector pin assignment

M23-12S1N8A80DU - Cable connector

1629212

<https://www.phoenixcontact.com/us/products/1629212>



I = current strength, ϑ = ambient temperature, 12x 8 A

M23-12S1N8A80DU - Cable connector



1629212

<https://www.phoenixcontact.com/us/products/1629212>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1629212>



cUL Recognized

Approval ID: E335019-20141210



UL Recognized

Approval ID: E335019-20141210

M23-12S1N8A80DU - Cable connector



1629212

<https://www.phoenixcontact.com/us/products/1629212>

Classifications

ECLASS

ECLASS-13.0	27440116
-------------	----------

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

M23-12S1N8A80DU - Cable connector



1629212
<https://www.phoenixcontact.com/us/products/1629212>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com