

1664073

<https://www.phoenixcontact.com/us/products/1664073>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 PCB connector, number of positions: 8, 100 Mbps

Your advantages

- Simplified Ethernet design process thanks to integrated filtering
- Reduced PCB complexity and reduced EMC risks
- Automated processing thanks to reflow solderability
- Ideal version for any application thanks to wide range of products
- Equipped for demanding areas of application thanks to industrial design

Commercial data

Item number	1664073
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AB12
Product key	ABNAFA
GTIN	4067923204171
Weight per piece (including packing)	8.86 g
Weight per piece (excluding packing)	6.1 g
Customs tariff number	85366930
Country of origin	CN

# CUC-IA4M-J1ST-AB/R4T-PL1 - RJ45 PCB connector



1664073

<https://www.phoenixcontact.com/us/products/1664073>

## Technical data

### Product properties

Product type	Data connector (device side)
Type	RJ45
Number of positions	8
Connection profile	RJ45
Housing shield springs	Yes
Number of slots	1
Type	Socket
Shielded	yes

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Rated surge voltage	1.5 kV
Rated surge voltage (III/3)	1.5 kV
Rated current	0.5 A
Insulation resistance	> 500 MΩ
Transmission medium	Copper
Transmission speed	10/100 Mbps

### Signaling

Status display	2 x LED (green, yellow)
Status display present	yes

### Dimensions

Width	15.9 mm
Height	17.13 mm
Length	21.35 mm
Installed height	13.63 mm
Orientation to PCB	90.00 °
Data pin length	3.50 mm

### Material specifications

Material Metal surface contact area (top layer)	Au (0.762 µm/30 µ")
Material Metal surface contact area (middle layer)	Ni (1,270 µm min / 50 µ" min)
Material Metal surface soldering area (middle layer)	Ni (1,016 µm min / 40 µ" min)
Material Metal surface soldering area (top layer)	Sn (3,048 µm min / 120 µ" min)
Material	Copper alloy (Housing (shielding))
	Ni (0.762 µm min / 30 µ" min) (Housing shielding (top layer))
	Sn (3,048 µm min / 120 µ" min) (Metal surface soldering area)

# CUC-IA4M-J1ST-AB/R4T-PL1 - RJ45 PCB connector



1664073

<https://www.phoenixcontact.com/us/products/1664073>

	shielding (top layer))
	LCP (Housing (female/insert))
Flammability rating according to UL 94	V0
Contact material	Phosphor bronze

## Cable/line

Halogen-free	yes
--------------	-----

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 750
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

## Environmental and real-life conditions

### Test specification

Specification	IEC 60603-7
---------------	-------------

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

## Mounting

Mounting type	THT wave
---------------	----------


### Processing notes

Classification temperature T <sub>c</sub>	260 °C
---	--------


## Packaging specifications

Type of packaging	Tray
-------------------	------

Drawings



Classification wave soldering profile



Circuit diagram

# CUC-IA4M-J1ST-AB/R4T-PL1 - RJ45 PCB connector



1664073

<https://www.phoenixcontact.com/us/products/1664073>

## Classifications

### ECLASS

ECLASS-13.0	27460201
-------------	----------

### ETIM

ETIM 9.0	EC002637
----------	----------

# CUC-IA4M-J1ST-AB/R4T-PL1 - RJ45 PCB connector



1664073

<https://www.phoenixcontact.com/us/products/1664073>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)