

CK2,5-ED-4,00BU AU - Crimp contact



1674846

<https://www.phoenixcontact.com/us/products/1674846>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 4 mm² ... 4 mm², AWG 12

Commercial data

Item number	1674846
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	AF7AID
GTIN	4017918135546
Weight per piece (including packing)	1.638 g
Weight per piece (excluding packing)	1.54 g
Customs tariff number	85366990
Country of origin	DE

CK2,5-ED-4,00BU AU - Crimp contact



1674846

<https://www.phoenixcontact.com/us/products/1674846>

Technical data

Notes

General	for HC-M-06..., HC-M-HV-, HC-M-08-, HC-M-20-, HC-A..., HC-B.., HC-BB..., HC-BBB..., and HC-HV contact carriers
---------	--

Mounting

Assembly note	At voltages of < 5 V and currents < 5 mA, gold-plated contacts are recommended. The quality of a crimp connection is determined by DIN EN 60352-2.
---------------	---

Product properties

Product type	Crimp contact
Series	HC-M-06
	HC-M-HV
	HC-M-08
	HC-A
	HC-BB
	HC-B
	HC-HV
	HC-M-20
	HC-K
	HC-BBB
	HC-Q
	HC-COM
	HC-M-EMV
Type	Individual female contact
Contact material type	turned

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Connection technology	Crimp connection
Conductor cross section	4 mm² ... 4 mm²
Connection cross section AWG	12
Stripping length of the individual wire	7.5 mm (9.5 mm at HC-M-HV...)
Conductor cross section flexible	4 mm² ... 4 mm²

Material specifications

Contact material	Copper alloy
Contact surface material	gold-plated

Dimensions

CK2,5-ED-4,00BU AU - Crimp contact



1674846

<https://www.phoenixcontact.com/us/products/1674846>

Mechanical characteristics

Contact diameter	2.5 mm
------------------	--------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------


CK2,5-ED-4,00BU AU - Crimp contact

1674846

<https://www.phoenixcontact.com/us/products/1674846>



Drawings



CK2,5-ED-4,00BU AU - Crimp contact

1674846

<https://www.phoenixcontact.com/us/products/1674846>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1674846>



EAC

Approval ID: RU C-DE.AI30.B.01102

CK2,5-ED-4,00BU AU - Crimp contact



1674846

<https://www.phoenixcontact.com/us/products/1674846>

Classifications

ECLASS

ECLASS-13.0	27440204
-------------	----------

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK2,5-ED-4,00BU AU - Crimp contact



1674846

<https://www.phoenixcontact.com/us/products/1674846>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com