


UM-2KS40/16AI/SI/RS/Z/SO225 - Input module



2319045

<https://www.phoenixcontact.com/us/products/2319045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



16-channel analog input module with spring-cage connection and redundant voltage supply.
Suitable for Yokogawa SAI 143 card.

Commercial data

Item number	2319045
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK2A8N
GTIN	4046356340656
Weight per piece (including packing)	803.3 g
Weight per piece (excluding packing)	300 g
Country of origin	DE

UM-2KS40/16AI/SI/RS/Z/SO225 - Input module



2319045

<https://www.phoenixcontact.com/us/products/2319045>

Technical data

Product properties

Product type	Interface module
No. of channels	16

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	30 V DC
Max. current carrying capacity per branch	1 A

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μ s)

Supported controller YOKOGAWA ProSafe-RS

Suitable I/O card	SAI143
-------------------	--------

Connection data

Field level

Connection method	Spring-cage connection
Number of connections	1
Number of positions	48
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	40
Tightening torque	0.5 Nm

Supply

Connection method	Spring-cage connection
Number of connections	1
Number of positions	6
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

UM-2KS40/16AI/SI/RS/Z/SO225 - Input module



2319045

<https://www.phoenixcontact.com/us/products/2319045>

Signaling

Status display present	yes, if the fuse fails
------------------------	------------------------

Dimensions

Item dimensions

Width	250 mm
Height	125.4 mm
Depth	97.9 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 55 °C
Altitude	< 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	Voltage monitoring on the module does not work in combination with upstream HESILED fuse terminal blocks with integrated LED display.
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

UM-2KS40/16AI/SI/RS/Z/SO225 - Input module



2319045

<https://www.phoenixcontact.com/us/products/2319045>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2319045>



EAC

Approval ID: RU*-DE.*08.B.01829*

UM-2KS40/16AI/SI/RS/Z/SO225 - Input module



2319045

<https://www.phoenixcontact.com/us/products/2319045>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	901712ba-32d1-4f6d-b8c4-4cc918352dda