

2905419

https://www.phoenixcontact.com/us/products/2905419

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in lightning arrester free of leakage current, in accordance with Type 1/Class I, for 3-phase power supply networks, with combined PE and N installed in one conductor (L1, L2, L3, PEN).

Your advantages

- · Surge protection family for universal use with optimum energy coordination from the lightning current arrester to the device protection
- Easy to maintain due to consistently pluggable protection modules
- · Excellent level of information provided by mechanical/visual status indicator and remote indication contact
- Optimum protective effect in the event of high-energy lightning currents, thanks to spark gap technology with low residual voltage characteristic
- · Low voltage protection level for direct protection of end devices in the main distribution area

Commercial data

Item number	2905419
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL01
Product key	CL1171
GTIN	4046356950091
Weight per piece (including packing)	1,150 g
Weight per piece (excluding packing)	1,063.5 g
Customs tariff number	85363010
Country of origin	DE



2905419

https://www.phoenixcontact.com/us/products/2905419

Technical data

Notes

\sim		_	
(ie	n	e	ra

Note	Max. single impulse: 100 kA (8/20 µs)
	SPD according to AS/NZS 1768 Cat. C3

Product properties

Product type	Combination type
Product family	SEC Family
IEC test classification	1/11
	T1 / T2
EN type	T1 / T2
IEC power supply system	TN-C
Туре	DIN rail module, two-section, divisible
Number of positions	3
Surge protection fault message	Optical, remote indicator contact

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Electrical properties

Operating current

Connection data

Nominal frequency f _N	50 Hz (60 Hz)
Indicator/remote signaling	
Connection name	Remote fault indicator contact
Switching function	Changeover contact
Operating voltage	12 V AC 250 V AC
	125 V DC (200 mA DC)

10 mA AC ... 1 A AC 1 A DC (30 V DC)

Connection method	Screw connection
Screw thread	M5
Tightening torque	4.5 Nm
Stripping length	18 mm
Conductor cross-section flexible	2.5 mm² 35 mm²
Conductor cross-section rigid	2.5 mm² 35 mm²
Conductor cross-section AWG	13 2
Connection method	Fork-type cable lug



2905419

https://www.phoenixcontact.com/us/products/2905419

Conductor cross-section flexible	1.5 mm² 16 mm²
Remote fault indicator contact	
Connection method	Plug-in/screw connection via COMBICON
Screw thread	M2
Tightening torque	0.25 Nm
Stripping length	7 mm
Conductor cross-section flexible	0.14 mm² 1.5 mm²
Conductor cross-section rigid	0.14 mm² 1.5 mm²
Conductor cross-section AWG	28 16

Dimensions

Dimensional drawing	95.2
Width	106.8 mm
Height	95.2 mm
Depth	74.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	6 Div.

Material specifications

Color (Male connector)	light gray (RAL 7035)
Color (Base element)	gray (RAL 7042)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA6.6-FR 20% GF
	PBT-FR
Material group	1
Housing material	PA 6.6-FR 20 % GF
	PBT-FR

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Mode of protection	L-PEN
Direction of action	3L-PEN
Nominal voltage U _N	240/415 V AC (TN-C)
Nominal frequency f _N	50 Hz (60 Hz)
Maximum continuous operating voltage U_C	350 V AC



2905419

https://www.phoenixcontact.com/us/products/2905419

Rated load current I _L	125 A (< 55 °C)
Nominal discharge current I_n (8/20) μs	25 kA
Maximum discharge current I _{max} (8/20) µs	50 kA
Impulse discharge current (10/350) μs, charge	12.5 As
Impulse discharge current (10/350) μs, specific energy	160 kJ/Ω
Impulse discharge current (10/350) μs, peak value I _{imp}	25 kA
Total discharge current I _{Total} (10/350) μs	75 kA
Follow current interrupt rating I _{fi}	50 kA
Short-circuit current rating I _{SCCR}	50 kA
Voltage protection level U _p	≤ 1.5 kV
Residual voltage U _{res}	≤ 1.5 kV (at I _n)
Front-of-wave sparkover voltage at 6 kV (1.2/50) µs	≤ 1.5 kV
TOV behavior at U _T	415 V AC (5 s / withstand mode)
	457 V AC (120 min / withstand mode)
Response time t _A	≤ 100 ns
Max. backup fuse with V-type through wiring	125 A (gG)
Max. backup fuse with branch wiring	315 A (gG)
Additional technical data	
Short-circuit current rating I _{SCCR}	100 kA (264 V AC)
Follow current interrupt rating I _{fi}	100 kA (264 V AC)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (only when all terminal points are used)
Ambient temperature (operation)	-40 °C 80 °C
Ambient temperature (storage/transport)	-40 °C 80 °C
Altitude	≤ 2000 m (amsl)
Permissible humidity (operation)	5 % 95 %
Shock (operation)	30g (Half-sine / 11 ms / 3x ±X, ±Y, ±Z)
Vibration (operation)	5g (5 - 500 Hz/2.5 h/X, Y, Z)

Approvals

UL specifications

Maximum continuous operating voltage MCOV (L-L)	700 V AC
Maximum continuous operating voltage MCOV (L-G)	350 V AC
Short-circuit current rating (SCCR)	50 kA
Voltage protection rating VPR (L-L)	2000 V
Voltage protection rating VPR (L-G)	1500 V
Nominal discharge current I _n	20 kA
Mode of protection	L-L
	L-G



2905419

https://www.phoenixcontact.com/us/products/2905419

Nominal voltage	240 V AC
	240/415 V AC
Rated load current I _L	50 A
Power distribution system	Delta
	Wye
Nominal frequency	50/60 Hz
SPD Type	2CA
UL indicator/remote signaling	
Operating voltage	125 V AC
AC operating current	1 A AC
UL connection data	
Tightening torque	40 lb _f -in.
Conductor cross-section AWG	3 2
Standards and regulations	
Standards/specifications	IEC 61643-11
Note	2011
EN 61643-11	
Standards/specifications	EN 61643-11
Note	2012
Mounting	
Mounting type	DIN rail: 35 mm





2905419

https://www.phoenixcontact.com/us/products/2905419

Drawings

Dimensional drawing







2905419

https://www.phoenixcontact.com/us/products/2905419


Product drawing






2905419

https://www.phoenixcontact.com/us/products/2905419







2905419

https://www.phoenixcontact.com/us/products/2905419

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2905419



cUL RecognizedApproval ID: FILE E 330181



UL Recognized

Approval ID: FILE E 330181



IECEE CB Scheme

Approval ID: NL-56588

CCA

Approval ID: NTR-NL 7726



KEMA-KEUR

Approval ID: 71-106982

UAE-RoHS

Approval ID: 23-10-88709



2905419

https://www.phoenixcontact.com/us/products/2905419

Classifications

ECLASS

	ECLASS-13.0	27171201		
	ECLASS-15.0	27171201		
ETIM				
	ETIM 9.0	EC000381		
UNSPSC				
	UNSPSC 21.0	39121600		



2905419

https://www.phoenixcontact.com/us/products/2905419

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com