

UK 10,3-HESI N 2POL - Fuse holder

3048483

<https://www.phoenixcontact.com/us/products/3048483>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse holder, fuse type: Ceramic, fuse type: 10.3 x 38 mm, nom. voltage: 690 V AC, nominal current: 32 A, number of positions: 2, connection method: Screw connection, Rated cross section: 16 mm², cross section: 1 mm² - 16 mm², mounting type: NS 35/7,5, NS 35/15, color: black

Your advantages

- For 10 x 38 fuse-links in accordance with IEC 60269-2
- Fuse holder for fuses up to 690 V AC
- Easy to bridge
- 2-pos. blocked version

Commercial data

Item number	3048483
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	BE12
Product key	BE1234
GTIN	4046356056052
Weight per piece (including packing)	92.96 g
Weight per piece (excluding packing)	117.26 g
Customs tariff number	85369095
Country of origin	TN

UK 10,3-HESI N 2POL - Fuse holder

3048483

<https://www.phoenixcontact.com/us/products/3048483>



Technical data

Product properties

Product type	Fuse terminal block
Number of positions	2
Number of connections	4
Number of rows	2

Insulation characteristics

Overtoltage category	III
Degree of pollution	3

Electrical properties

Fuse type	Ceramic
Rated surge voltage	6 kV
Fuse	10.3 x 38 mm

Connection data

Number of connections per level	2
Nominal cross section	16 mm ²
Connection method	Screw connection
Screw thread	M5
Tightening torque	2 Nm
Stripping length	15 mm
Internal cylindrical gage	B6 A7
Connection in acc. with standard	IEC 60947-1 / -3
Conductor cross-section rigid	1 mm ² ... 16 mm ²
Cross section AWG	18 ... 6 (converted acc. to IEC)
Conductor cross-section flexible	1 mm ² ... 16 mm ²
Conductor cross-section, flexible [AWG]	18 ... 6 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	1.5 mm ² ... 10 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	1.5 mm ² ... 10 mm ²
2 conductors with same cross section, solid	1 mm ² ... 6 mm ²
2 conductors with same cross section, flexible	1 mm ² ... 6 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.75 mm ² ... 4 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm ² ... 4 mm ²
Nominal current	32 A (the current and voltage are determined by the fuse)
Maximum load current	32 A (the current and voltage are determined by the fuse)
Nominal voltage	690 V AC (the current and voltage are determined by the fuse)
Nominal cross section	16 mm ²

Dimensions

UK 10,3-HESI N 2POL - Fuse holder

3048483

<https://www.phoenixcontact.com/us/products/3048483>



Width	35.1 mm
Height	79.3 mm
Depth	61.1 mm
Depth on NS 35/7,5	64 mm
Depth on NS 35/15	71.5 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V2
Insulating material group	III
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Standards and regulations

Connection in acc. with standard	IEC 60947-1 / -3
----------------------------------	------------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15

UK 10,3-HESI N 2POL - Fuse holder


3048483

<https://www.phoenixcontact.com/us/products/3048483>



Drawings

Circuit diagram



UK 10,3-HESI N 2POL - Fuse holder

3048483

<https://www.phoenixcontact.com/us/products/3048483>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3048483>



UL Recognized

Approval ID: E244294



CSA

Approval ID: 274201

UK 10,3-HESI N 2POL - Fuse holder

3048483

<https://www.phoenixcontact.com/us/products/3048483>



Classifications

ECLASS

ECLASS-13.0	27250113
ECLASS-15.0	27250113

ETIM

ETIM 9.0	EC000899
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UK 10,3-HESI N 2POL - Fuse holder

3048483

<https://www.phoenixcontact.com/us/products/3048483>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com