


# CARRIER 35-13 - End bracket



3059117

<https://www.phoenixcontact.com/us/products/3059117>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End bracket, material: PA, mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3059117       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1Z2X        |
| GTIN                                 | 4055626082486 |
| Weight per piece (including packing) | 9.975 g       |
| Weight per piece (excluding packing) | 9.6 g         |
| Customs tariff number                | 85389099      |
| Country of origin                    | CN            |

# CARRIER 35-13 - End bracket

3059117

<https://www.phoenixcontact.com/us/products/3059117>



## Technical data

### Product properties

|              |             |
|--------------|-------------|
| Product type | End bracket |
|--------------|-------------|

### Dimensions

|                    |         |
|--------------------|---------|
| Width              | 13 mm   |
| Height             | 53.3 mm |
| Depth on NS 32     | 52.1 mm |
| Depth on NS 35/7,5 | 47.1 mm |
| Depth on NS 35/15  | 54.6 mm |
| Length             | 53.3 mm |

### Material specifications

|                                                                         |                 |
|-------------------------------------------------------------------------|-----------------|
| Color                                                                   | gray (RAL 7042) |
| Material                                                                | PA              |
| Flammability rating according to UL 94                                  | V0              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

### Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |
|               | NS 32     |

# CARRIER 35-13 - End bracket



3059117

<https://www.phoenixcontact.com/us/products/3059117>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250302 |
| ECLASS-15.0 | 27250302 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001041 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CARRIER 35-13 - End bracket



3059117

<https://www.phoenixcontact.com/us/products/3059117>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)