

# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable



1435645

<https://www.phoenixcontact.com/us/products/1435645>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug angled M12 SPEEDCON, coding: A, with 1 LED, on Valve connector CI (9.4 mm), with 1 LED, Wiring: Z diode, cable length: 0.6 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Save time, thanks to installation with SPEEDCON fast locking system
- Convenient: increased machine availability thanks to quick and easy diagnostics
- Our standard: robust halogen-free PUR cable

## Commercial data

Item number	1435645
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF07
Product key	AF1DOA
Catalog page	Page 228 (C-2-2019)
GTIN	4046356413893
Weight per piece (including packing)	42.9 g
Weight per piece (excluding packing)	39.9 g
Customs tariff number	85444290
Country of origin	PL

# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable



1435645

<https://www.phoenixcontact.com/us/products/1435645>

## Technical data

### Product properties

Product type	Sensor/actuator cable with valve connector
Application	Standard
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Connection data

#### Conductor connection

Tightening torque	0.4 Nm (M12 connector)
	0.6 Nm (Valve connector)

### Material specifications

Flammability rating according to UL 94	HB
Seal material	TPU
Material housing valve plug	TPU
Material of grip body	TPU
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Contact material	CuSn
Valve plug contact insert material	PA 6.6
Contact surface material	Sn
Material for screw connection	Zinc die-cast, nickel-plated

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	24 V AC
	24 V DC
Nominal current $I_N$	4 A

### Valve connector characteristics

Fixing screws	M3 x 29
Pulse power	40 W (at 100 $\mu$ s square-wave pulse)
Terminal voltage	70 V (at 2 mA constant current)
Reverse voltage	50 V

# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable



1435645

<https://www.phoenixcontact.com/us/products/1435645>

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 100 (M12 connector)
-----------------------------	-----------------------

## Signaling

Status display	1 LED
Status display present	yes

## Connector

### Connection 1

Type	Plug angled M12 SPEEDCON
Number of positions	3
Locking type	SPEEDCON
Coding type	A


### Connection 2

Type	Valve connector CI (9.4 mm)
Number of positions	3
Material	CuSn (Contact)
	Sn (Contact surface)
	PA 6.6 (Contact carrier)
	TPU (Housing)
Protective circuit	Z diode

## Cable/line

Cable length	0.6 m
--------------	-------

### PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	30 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	28x 0.15 mm
AWG signal line	20

# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable



1435645

<https://www.phoenixcontact.com/us/products/1435645>

Conductor cross section	3x 0.5 mm <sup>2</sup>
Wire diameter incl. insulation	1.5 mm ±0.05 mm (Signal line)
External cable diameter	4.50 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	39 Ω/km (at 20 °C)
Insulation resistance	min. 20 MΩ*km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 1200 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	22.5 mm
Smallest bending radius, movable installation	45 mm
Dynamic load capacity (bending)	Max. bending cycles: 15000000, Bending radius: 50 mm, Traversing path: 0.9 m, Traversing rate: 5 m/s, Acceleration: 30 m/s <sup>2</sup>
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	according to DIN VDE 0482
	According to DIN EN 50265-2-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	largely oil-resistant
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-20 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-20 °C ... 85 °C (Valve connector)
	-40 °C ... 80 °C (cable, fixed installation)
	-15 °C ... 80 °C (Cable, flexible installation)

## Standards and regulations

### M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable

1435645

<https://www.phoenixcontact.com/us/products/1435645>

## Drawings

Dimensional drawing




M12 x 1 male plug, angled

# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable

1435645


<https://www.phoenixcontact.com/us/products/1435645>

Dimensional drawing



Valve connector, type CI

Dimensional drawing




Valve connector, type CI, side view

# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable

1435645


<https://www.phoenixcontact.com/us/products/1435645>

Schematic diagram



Pin assignment M12 plug, 3-pos., valve connector

Schematic diagram




Valve connector connector pin assignment, type CI

# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable

1435645

<https://www.phoenixcontact.com/us/products/1435645>



Contact assignment of M12 plug and valve connector




# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable



1435645  
<https://www.phoenixcontact.com/us/products/1435645>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1435645>

 <b>CSAus</b> Approval ID: 13631	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	24 V	4 A	-	-

# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable



1435645  
<https://www.phoenixcontact.com/us/products/1435645>

## Classifications

### ECLASS

ECLASS-13.0	27060312
-------------	----------

### ETIM

ETIM 9.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

# SAC-3P-MR/ 0,6-PUR/CI-1L-Z SCO - Sensor/actuator cable



1435645

<https://www.phoenixcontact.com/us/products/1435645>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	0.525 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)