

# AI 0,5-8 WH S1 - Ferrule

1200104

<https://www.phoenixcontact.com/us/products/1200104>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Taped ferrules, 0.5 mm<sup>2</sup>, sleeve length 8 mm, with plastic collar, according to DIN 46228-4, white, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 50 sleeves per strip.

## Commercial data

Item number	1200104
Packing unit	500 pc
Minimum order quantity	500 pc
Sales key	BH34
Product key	BH3415
Catalog page	Page 415 (C-3-2019)
GTIN	4055626043012
Weight per piece (including packing)	0.082 g
Weight per piece (excluding packing)	0.082 g
Customs tariff number	85369010
Country of origin	DE

# AI 0,5-8 WH S1 - Ferrule

1200104

<https://www.phoenixcontact.com/us/products/1200104>



## Technical data

### Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	For processing with our CRIMPFOX 4 IN 1
	UL certified
	Made from tin-plated electrolytic copper
	Design in accordance with DIN 46228-1 and UL 486F
	With "Easy Entry" (conical insertion area)
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

### Connection data

#### Conductor connection

Conductor cross section flexible max.	0.5 mm <sup>2</sup>
Conductor cross section AWG max.	20
Stripping length	11 mm

### Dimensions

Dimensional drawing	
Sleeve length	14 mm
Length contact range	8 mm
Maximum stripping length	11 mm
Ferrule diameter	1.1 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.25 mm
Inner dimensions of the insulating collar	2.5 mm

### Material specifications

Color	white (RAL 9010)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

### Mechanical properties

# AI 0,5-8 WH S1 - Ferrule



1200104

<https://www.phoenixcontact.com/us/products/1200104>

## Technical data

Sleeve length	14 mm
---------------	-------

## Environmental and real-life conditions

### Ambient conditions

Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

## Standards and regulations

Design according to standard	DIN 46228-4, UL 486F-E
------------------------------	------------------------

## Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)


# AI 0,5-8 WH S1 - Ferrule

1200104

<https://www.phoenixcontact.com/us/products/1200104>



## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1200104>



**cULus Listed**

Approval ID: E488001

# AI 0,5-8 WH S1 - Ferrule



1200104

<https://www.phoenixcontact.com/us/products/1200104>

## Classifications

### ECLASS

ECLASS-13.0	27400201
-------------	----------

### ETIM

ETIM 9.0	EC000005
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# AI 0,5-8 WH S1 - Ferrule



1200104  
<https://www.phoenixcontact.com/us/products/1200104>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)