

# PAIS-4-FIX RD - Test adapter

3032793

<https://www.phoenixcontact.com/us/products/3032793>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test adapter, Do not plug in while the power is connected, for 4 mm test plug and terminal blocks with 5.2 mm, 6.2 mm, and 8.2 mm pitch, number of positions: 1, color: red

## Your advantages

- Make contact and latch securely to any point in the function shaft
- Test adapter for accommodating safety test plugs with a 4 mm diameter

## Commercial data

Item number	3032793
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE2Z3X
GTIN	4046356996709
Weight per piece (including packing)	2.47 g
Weight per piece (excluding packing)	2.36 g
Customs tariff number	85366990
Country of origin	PL

# PAIS-4-FIX RD - Test adapter

3032793

<https://www.phoenixcontact.com/us/products/3032793>



## Technical data

### Notes

General	Do not plug in while the power is connected
General	Latching coding element, therefore only suitable for being plugged in once
General	Latching testing accessories, therefore only suitable for being plugged in once

### Product properties

Product type	Test socket
Number of positions	1

### Electrical properties

Maximum load current	10 A
Max. voltage	250 V

### Connection data

Maximum load current	10 A
Connection method	Plug-in connection

### Dimensions

Width	6 mm
Height	6.5 mm
Depth	53.3 mm
Diameter	5.8 mm
Pin diameter	2.4 mm

### Material specifications

Color	red (RAL 3001)
Material	Copper alloy
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	1
-----------------------------	---

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
---------------------------------	--

# PAIS-4-FIX RD - Test adapter



3032793

<https://www.phoenixcontact.com/us/products/3032793>

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

# PAIS-4-FIX RD - Test adapter



3032793

<https://www.phoenixcontact.com/us/products/3032793>

## Classifications

### ECLASS

ECLASS-13.0	27250304
-------------	----------

### ETIM

ETIM 9.0	EC002555
----------	----------

### UNSPSC

UNSPSC 21.0	20122000
-------------	----------

# PAIS-4-FIX RD - Test adapter



3032793

<https://www.phoenixcontact.com/us/products/3032793>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)