

SPE-T1-M8FSF/2,0-97B/M8FSF - Network cable



1217530
<https://www.phoenixcontact.com/us/products/1217530>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Single Pair Ethernet CAT A (10 Mbps), 2-position, PVC, black, shielded (Advanced Shielding Technology), Socket straight M8-SPE / IP67, on Socket straight M8-SPE / IP67, cable length: 2 m

Product description

Single Pair Ethernet M8 patch cable

Your advantages

- Future-proof: standardized connectors in accordance with IEC 63171-5 (IP67)
- Easily integrated: Male and female versions for established inductive sensors and flying leads
- Efficient: Device connectors for SMD, THR, and wave soldering processes enable automated processing
- Straightforward servicing: M8 connectors are compatible with IP20 connectors for SPE
- Safely shielded: patch cables with Advanced Shielding Technology

Commercial data

Item number	1217530
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF02
Product key	AF1BJI
GTIN	4063151298890
Weight per piece (including packing)	94.2 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444290
Country of origin	PL

SPE-T1-M8FSF/2,0-97B/M8FSF - Network cable



1217530
<https://www.phoenixcontact.com/us/products/1217530>

Technical data

Product properties

Product type	Data cable preassembled
Application	Standard
Sensor type	Single Pair Ethernet
Number of positions	2
No. of cable outlets	1
Shielded	yes

Insulation characteristics

Overvoltage category	I
----------------------	---

Interfaces

Bus system	Ethernet
Signal type/category	Single Pair Ethernet CAT A (ISO/IEC 63171), 10 Mbps

Signaling

Status display	no
Status display present	no

Electrical properties

Nominal voltage U_N	72 V DC
Transmission medium	Copper

Material specifications

Flammability rating according to UL 94	V0
--	----


Connection data

Pin assignment

Contact Color (signal designation) Contact (optional)	1 WH (RX/TX+) 1
	2 BU (RX/TX-) 2

Connector

Connection 1

Dimensional drawing	
---------------------	--

SPE-T1-M8FSF/2,0-97B/M8FSF - Network cable




1217530

<https://www.phoenixcontact.com/us/products/1217530>

	Pin assignment, Single Pair Ethernet, 2 pos.
Type	M8 Socket, straight, 2-position, shielded (Advanced Shielding Technology), Keying: SPE
Number of positions	2
Shielded	yes
Shielding	Advanced Shielding Technology
Signal type/category	Single Pair Ethernet CAT B (IEC 63171)
Insertion/withdrawal cycles	≥ 100
Insulation resistance	≥ 100 MΩ
Overvoltage category	II
Degree of pollution	3
Tightening torque	0.2 Nm
Material Contact	Cu
Material Contact surface	Ni/Au
Material Contact carrier	PP
Material Screw connection	Die-cast zinc, nickel-plated
Material Grip body	TPU, hardly inflammable, self-extinguishing
Material Seal	FKM
Flammability rating according to UL 94	V0
Degree of protection	IP65 IP67
Ambient temperature (operation)	-25 °C ... 85 °C
Standard designation	M8 connector
Standards/regulations	IEC 63171-5

Connection 2

Dimensional drawing	 <p>Pin assignment, Single Pair Ethernet, 2 pos.</p>
Type	M8 Socket, straight, 2-position, shielded (Advanced Shielding Technology), Keying: SPE
Number of positions	2
Shielded	yes
Shielding	Advanced Shielding Technology
Signal type/category	Single Pair Ethernet CAT B (IEC 63171)
Insertion/withdrawal cycles	≥ 100
Insulation resistance	≥ 100 MΩ

SPE-T1-M8FSF/2,0-97B/M8FSF - Network cable



1217530


<https://www.phoenixcontact.com/us/products/1217530>

Overvoltage category	II
Degree of pollution	3
Tightening torque	0.2 Nm
Material Contact	Cu
Material Contact surface	Ni/Au
Material Contact carrier	PP
Material Screw connection	Die-cast zinc, nickel-plated
Material Grip body	TPU, hardly inflammable, self-extinguishing
Material Seal	FKM
Flammability rating according to UL 94	V0
Degree of protection	IP65 IP67
Ambient temperature (operation)	-25 °C ... 85 °C
Standard designation	M8 connector
Standards/regulations	IEC 63171-5

Cable/line

Cable length	2 m
--------------	-----

Single Pair Ethernet PUR flexible, black [97B]

Dimensional drawing	
UL AWM Style	2095 (80°C/300 V)
Number of positions	2
Shielded	yes
Cable type	Single Pair Ethernet PUR flexible, black [97B]
Conductor structure	1 x 2 x AWG 22/7, S/FTP
Conductor structure signal line	7x
AWG signal line	22
Conductor cross section	2x 0.34 mm ²
Wire diameter incl. insulation	1.65 mm
External cable diameter	5.10 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Tin-plated Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	white, blue
Thickness, outer sheath	0.55 mm

SPE-T1-M8FSF/2,0-97B/M8FSF - Network cable



1217530

<https://www.phoenixcontact.com/us/products/1217530>

Twisted pairs	2 cores to the pair
Overall twist	1 pair with fillers twisted horizontally
Optical shield covering	80 %
Max. conductor resistance	$\leq 59.4 \Omega/\text{km}$
Insulation resistance	$\geq 5 \text{ G}\Omega \cdot \text{km}$
Wave impedance	$100 \Omega \pm 15 \Omega$ (at 20 MHz)
Nominal voltage, cable	300 V
Minimum bending radius, fixed installation	4 x D
Smallest bending radius, fixed installation	21 mm
Flame resistance	According to FT-2
Ambient temperature (operation)	-20 °C ... 80 °C (cable, fixed installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67


Standards and regulations

M8

Standard designation	M8 connector
Standards/specifications	IEC 63171-5
Note	T1-SPE

Drawings

Dimensional drawing




Socket M8 x 1, straight

1217530

<https://www.phoenixcontact.com/us/products/1217530>

Schematic diagram



Pin assignment, Single Pair Ethernet, 2 pos.

SPE-T1-M8FSF/2,0-97B/M8FSF - Network cable



1217530

<https://www.phoenixcontact.com/us/products/1217530>

Classifications

ECLASS

ECLASS-13.0	27060307
-------------	----------

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SPE-T1-M8FSF/2,0-97B/M8FSF - Network cable



1217530

<https://www.phoenixcontact.com/us/products/1217530>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	4.109 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com