

PSR-M-B2-XC-SDI8-SDO4-DO4-PI - Safety module



1337849

<https://www.phoenixcontact.com/us/products/1337849>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Configurable safety module (basic module), 8 safe inputs, 4 safe outputs, 4 reset inputs or 4 signal outputs, 4 clock outputs, can be extended via TBUS, up to SIL 3, Cat. 4/PL e, plug-in Push-in terminal block, TBUS connector not included

Product description

The configurable and individually scalable PSRmodular safety system is a flexible safety solution for monitoring your machine or system. The freely configurable base module is used to monitor various pieces of safety equipment such as emergency stop, safety doors, and light grids. The base module has safe inputs and outputs, as well as signal outputs and clock outputs.

Your advantages

- Cost-effective safety solution with a high level of adaptability to individual requirements
- Fast startup, thanks to easy hardware and software configuration
- Machine downtimes minimized with comprehensive, easy-to-understand diagnostics
- Flexible extension with safe inputs and outputs
- Possibility of connecting fieldbus gateways for bidirectional communication between the base module and the higher-level controller
- Low housing width of just 22.6 mm
- Tool-free and time-saving installation thanks to Push-in technology
- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- Suitable for elevator applications in accordance with EN 81-20
- Corrosion protection through protective coating on the PCB
- Suitable for ATEX Zone 2 or Class I Zone 2

Commercial data

Item number	1337849
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN02
Product key	DNA361
GTIN	4063151640835
Weight per piece (including packing)	180.1 g
Weight per piece (excluding packing)	180.1 g
Customs tariff number	85371098
Country of origin	IT

1337849

<https://www.phoenixcontact.com/us/products/1337849>

Technical data

Product properties

Product type	Safety device
Application	Emergency stop
	Light grid
	Safety door
	Safe shutdown
Control	1 and 2 channel

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Times

Response time	see user manual
Restart time	min. 5 s (Boot time)
	max. 10 s (Boot time)

Electrical properties

Maximum power dissipation for nominal condition	7.48 W (with max. permissible load)
Nominal operating mode	100% operating factor
Interfaces	DIN rail TBUS for connection to the master module, not supplied as standard
Rated surge voltage/insulation	See data sheet, section "Insulation coordination".

Supply

Designation	A1/A2
Rated control circuit supply voltage U_S	19.2 V DC ... 28.8 V DC
Rated control circuit supply voltage U_S	24 V DC -20 % / +20 % (external fuse, typically 4 A)
Rated control supply current I_S	typ. 55 mA (Outputs inactive)
Power consumption at U_S	typ. 1.32 W (Outputs inactive)
Inrush current	9.16 A ($\Delta t = 0.5$ ms at U_S)
Filter time	typ. 5 ms (in the event of voltage dips at U_S)
Protective circuit	Serial protection against polarity reversal

Input data

Digital: IN1, IN2, IN3, IN4, IN5, IN6, IN7, IN8

Description of the input	Safety-related digital inputs
	NPN
Number of inputs	8
Input voltage range "0" signal	0 V DC ... 5 V DC (for safe Off)
Input voltage range "1" signal	11 V DC ... 28.8 V DC
Input current range "0" signal	< 0.2 mA
Inrush current	max. 524 mA ($\Delta t = 6$ μ s at U_S)

Filter time	min. 3 ms (adjustable)
	max. 250 ms (adjustable)
	Test pulse rate $\geq 2x$ set filter time, min. Test pulse rate = 10 ms
	max. 3 ms (Test pulse rate $\geq 10x$ configured filter time for low test pulse)
	max. 250 ms (Test pulse rate $\geq 10x$ configured filter time for high test pulse)
Cable length	max. 100 m (per input)
Max. permissible overall conductor resistance	max. 1.2 k Ω (Input and reset circuit at U_S)
Current consumption	typ. 3.7 mA (typ. with U_S)
	max. 4.6 mA (at a control voltage of 28.8 V DC)

Digital: Reset inputs (FBK)

Description of the input	configurable (as signal output or reset input)
	NPN, digital
Number of inputs	4
Input voltage range "0" signal	0 V DC ... 5 V DC (for safe Off)
Input voltage range "1" signal	11 V DC ... 28.8 V DC
Input current range "0" signal	< 0.2 mA
Inrush current	max. 906.53 mA ($\Delta t = 10 \mu s$ at U_S)
Filter time	250 ms (constant)
	< 250 ms (Test pulse duration)
	> 1 s (Test pulse rate)
Cable length	max. 100 m
Max. permissible overall conductor resistance	1.2 k Ω (Input and reset circuit at U_S)
Current consumption	typ. 5.7 mA (typ. with U_S)
	max. 7 mA (at a control voltage of 28.8 V DC)

Output data

Digital: O1, O2, O3, O4

Output description	Safety-related digital outputs
	PNP, OSSD, digital
	IEC 61131-2 type 0.25 (observe limiting continuous current)
Number of outputs	4
Short-circuit protection	no
Output voltage	< 0.3 V (Low state)
Leakage current	< 500 μA (Low state)
Cable length	max. 100 m
Max. capacitive load	max. 820 nF
Max. inductive load	See "Protective circuit"
Limiting continuous current	400 mA (per channel)
	1.6 A (Total current of all safe digital outputs)
Inrush current	max. 600 mA ($\Delta t = 25 ms$ at U_S)
Nominal output voltage	24 V DC (Supply via A1)

PSR-M-B2-XC-SDI8-SDO4-DO4-PI - Safety module



1337849

<https://www.phoenixcontact.com/us/products/1337849>

Nominal output voltage range	18.6 V DC ... 28.2 V DC ($U_S - 0.7$ V)
Switching frequency	max. $1/4 \times t_{\text{Cycle}}$ [Hz]
Test pulses	< 235 μ s (Test pulse width of low test pulses)
	≥ 650 ms (Test pulse rate for low test pulse)
	< 150 μ s (Test pulse width, high test pulse)
	≥ 1.5 s (Test pulse rate, high test pulse)
Discharging circuit	Yes, internal

Signal: MO1, MO2, MO3, MO4

Output description	PNP, digital, IEC 61131-2 type 0.1
	non-safety-related, configurable (as signal output or reset input)
Number of outputs	4
Output voltage when switched off	max. 0.1 V
Output voltage range	18.2 V DC ... 27.8 V DC ($U_S - 1$ V)
Voltage	24 V DC (via A1)
Maximum inrush current	1.1 A ($\Delta t = 3$ s at U_S)
Limiting continuous current	100 mA (per channel)
	400 mA (Total current of all digital signal outputs)
Leakage current	max. 4.5 mA (Low state)
Switching frequency	max. $1/4 \times t_{\text{Cycle}}$ [Hz]
Short-circuit protection	Yes (self-limitation at 1.1 A)
Discharging circuit	No
Cable length	max. 100 m

Clock: T1, T2, T3, T4

Output description	PNP, digital, IEC 61131-2 type 0.1
Number of outputs	4
Voltage	24 V DC (via A1)
Maximum inrush current	1.1 A ($\Delta t = 3$ s at U_S)
Limiting continuous current	100 mA (per channel)
	400 mA (Total current of all outputs)
Test pulses	≤ 200 μ s (Test pulse duration)
	Test pulse rate = $8 \times t_{\text{Cycle}}$ [ms]
Short-circuit protection	Yes (self-limitation at 1.1 A)
Cable length	max. 100 m
Max. capacitive load	max. 470 nF
Max. inductive load	max. 2.4 mH
Discharging circuit	Yes, internal

Connection data

Connection technology

pluggable	yes
-----------	-----

Conductor connection

Connection method	Push-in connection
-------------------	--------------------

PSR-M-B2-XC-SDI8-SDO4-DO4-PI - Safety module



1337849

<https://www.phoenixcontact.com/us/products/1337849>

Conductor cross section rigid	0.2 mm² ... 2.5 mm²
Conductor cross section flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section AWG	24 ... 14
Stripping length	10 mm

Interfaces

Data: Service interface

Connection method	USB 2.0 Hi-Speed
Number of connections	1

Data: Local bus

Note	via the PSR-TBUS DIN rail connector
------	-------------------------------------

Signaling

Status display	1 x LED (green), 1 x LED (orange), 1 x LED (blue)
	4 x LED (green, yellow, red)
	12 x LED (yellow)
Operating voltage display	1 x LED (green)
Error indication	2 x LED (red)

Dimensions

Width	22.61 mm
Height	107.74 mm
Depth	113.6 mm

Material specifications

Color (Housing)	yellow (RAL 1018)
Housing material	Polyamide PA non-reinforced

Characteristics

Safety data: EN ISO 13849

Performance level (PL)	e (2-channel wiring)
	d (1-channel wiring)

Safety data: IEC 61508 - High-demand for 2-channel wiring

Safety Integrity Level (SIL)	3
------------------------------	---

Safety data: IEC 61508 - High-demand for 1-channel wiring

Safety Integrity Level (SIL)	2
------------------------------	---

Safety data: EN IEC 62061

Safety Integrity Level (SIL)	3 (2-channel wiring)
	2 (1-channel wiring)

Environmental and real-life conditions

1337849

<https://www.phoenixcontact.com/us/products/1337849>

Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-20 °C ... 70 °C (observe derating)
Ambient temperature (operation) (ATEX)	-20 °C ... 50 °C (When used in potentially explosive areas. Observe derating)
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Maximum altitude	≤ 2000 m (Above sea level)
Max. permissible humidity (storage/transport)	95 % (non-condensing)
Max. permissible relative humidity (operation)	95 % (non-condensing)
Shock	10g for $\Delta t = 16$ ms (continuous shock, 1000 shocks in each space direction)
Vibration (operation)	10 Hz ... 150 Hz, 2g

Approvals

ATEX

Note	T4: for $-20^{\circ}\text{C} \leq T_{\text{amb}} \leq \text{ⓈⓉⓉ}^{\circ}\text{C}$
------	---

UL Ex, USA / Canada

Identification	Class I, Div. 2, Groups A, B, C, D T4
Note	T4: for $-20^{\circ}\text{C} \leq T_{\text{amb}} \leq \text{ⓈⓉⓉ}^{\circ}\text{C}$

CE

Identification	CE-compliant
----------------	--------------

Environmental simulation test

Identification	G3
Certificate	ISA-S71.04

DNV

Identification	C, EMC2
----------------	---------


Mounting

Mounting type	DIN rail mounting
Assembly note	Observe derating
Mounting position	vertical or horizontal

1337849

<https://www.phoenixcontact.com/us/products/1337849>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1337849>

DNV

Approval ID: TAA000039N



cULus Listed

Approval ID: E238705



cULus Listed

Approval ID: E196811

Classifications

ECLASS

ECLASS-13.0	27371819
-------------	----------

ETIM

ETIM 9.0	EC001449
----------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com