

PATG HF 1/12 - Conductor marker carrier



1014045

<https://www.phoenixcontact.com/us/products/1014045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, transparent/black, unmarked, cable diameter range: 1.3 ... 2.8 mm, mounting type: slide-on, text field height: 4 mm, text field width: 12 mm

Your advantages

- The PATG HF... sleeve is a captive marker carrier
- These conductor marking systems consist of marker carriers and insert labels
- Comprehensive approvals ensure international use
- The use of high-quality plastics supports the most stringent demands of the rail industry and the automotive industry
- The corresponding UCT-WMT... and UC-WMT... insert labels are used for marking
- Due to the plastic properties of the PATG HF..., high-quality fluid printing of the UC-WMT... with the BLUEMARK... is required

Commercial data

Item number	1014045
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Sales key	BG12
Product key	BG221A
GTIN	4046356779326
Weight per piece (including packing)	0.152 g
Weight per piece (excluding packing)	0.148 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	12 mm
Height	5.7 mm
Depth	5.7 mm

Material specifications

Color	multicolored
	transparent
	black (RAL 9005)
Material	TPU
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	1.3 mm ... 2.8 mm
-------------------------	-------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed

PATG HF 1/12 - Conductor marker carrier



1014045

<https://www.phoenixcontact.com/us/products/1014045>

IRM 902	Test passed
---------	-------------

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

Standards and regulations

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	slide-on
---------------	----------

PATG HF 1/12 - Conductor marker carrier



1014045

<https://www.phoenixcontact.com/us/products/1014045>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 9.0	EC002248
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PATG HF 1/12 - Conductor marker carrier



1014045

<https://www.phoenixcontact.com/us/products/1014045>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.004 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com