

SAC-3P-M 8MS/1,5-PVC/M 8FR - Sensor/actuator cable



1415889  
<https://www.phoenixcontact.com/us/products/1415889>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black RAL 9005, Plug straight M8, coding: A, on Socket angled M8, coding: A, cable length: 1.5 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1415889       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF01          |
| Product key                          | AF1BBA        |
| GTIN                                 | 4055626054582 |
| Weight per piece (including packing) | 48.4 g        |
| Weight per piece (excluding packing) | 41.272 g      |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

# SAC-3P-M 8MS/1,5-PVC/M 8FR - Sensor/actuator cable



1415889

<https://www.phoenixcontact.com/us/products/1415889>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 3                     |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Seal material                          | NBR                                         |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 48 V AC                    |
|                       | 60 V DC                    |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connector

#### Connection 1

|                     |                  |
|---------------------|------------------|
| Type                | Plug straight M8 |
| Number of positions | 3                |
| Coding type         | A                |

#### Connection 2

# SAC-3P-M 8MS/1,5-PVC/M 8FR - Sensor/actuator cable



1415889


<https://www.phoenixcontact.com/us/products/1415889>

|                     |                  |
|---------------------|------------------|
| Type                | Socket angled M8 |
| Number of positions | 3                |
| Coding type         | A                |

## Cable/line

|              |       |
|--------------|-------|
| Cable length | 1.5 m |
|--------------|-------|

## PVC black [PVC]

|                                             |                                                                                                 |
|---------------------------------------------|-------------------------------------------------------------------------------------------------|
| Dimensional drawing                         |               |
| Cable weight                                | 29 kg/km                                                                                        |
| Number of positions                         | 3                                                                                               |
| Shielded                                    | no                                                                                              |
| Cable type                                  | PVC black [PVC]                                                                                 |
| Conductor structure signal line             | 14x 0.15 mm                                                                                     |
| AWG signal line                             | 24                                                                                              |
| Conductor cross section                     | 3x 0.25 mm² (Signal line)                                                                       |
| Wire diameter incl. insulation              | 1.17 mm ±0.05 mm                                                                                |
| External cable diameter                     | 4.20 mm ±0.15 mm                                                                                |
| Outer sheath, material                      | PVC                                                                                             |
| External sheath, color                      | black RAL 9005                                                                                  |
| Conductor material                          | Bare Cu litz wires                                                                              |
| Material wire insulation                    | PVC                                                                                             |
| Single wire, color                          | brown, blue, black                                                                              |
| Thickness, insulation                       | ≥ 0.23 mm (Core insulation)                                                                     |
| Thickness, outer sheath                     | ≥ 0.76 mm                                                                                       |
| Overall twist                               | 3 wires, twisted                                                                                |
| Max. conductor resistance                   | max. 79 Ω/km (at 20 °C)                                                                         |
| Insulation resistance                       | ≥ 100 MΩ*km (at 20 °C)                                                                          |
| Nominal voltage, cable                      | ≥ 300 V                                                                                         |
| Test voltage                                | ≤ 3000 V                                                                                        |
| Smallest bending radius, fixed installation | 13 mm                                                                                           |
| Flame resistance                            | As per UL-Style 2464                                                                            |
| Resistance to oil                           | EN 60811-2-1                                                                                    |
| Ambient temperature (operation)             | -25 °C ... 80 °C (cable, fixed installation)<br>-10 °C ... 80 °C (Cable, flexible installation) |

## Environmental and real-life conditions

# SAC-3P-M 8MS/1,5-PVC/M 8FR - Sensor/actuator cable



1415889

<https://www.phoenixcontact.com/us/products/1415889>

## Ambient conditions

|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Degree of protection                                              | IP65                             |
|                                                                   | IP67                             |
|                                                                   | IP68                             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket) |

## Standards and regulations

### M8

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M8 connector    |
| Standards/specifications | IEC 61076-2-104 |

# SAC-3P-M 8MS/1,5-PVC/M 8FR - Sensor/actuator cable



1415889

<https://www.phoenixcontact.com/us/products/1415889>


## Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Dimensional drawing




Socket M8 x 1, angled

# SAC-3P-M 8MS/1,5-PVC/M 8FR - Sensor/actuator cable

1415889


<https://www.phoenixcontact.com/us/products/1415889>

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

Schematic diagram




Pin assignment M8 socket, 3-pos., view female side

# SAC-3P-M 8MS/1,5-PVC/M 8FR - Sensor/actuator cable

1415889


<https://www.phoenixcontact.com/us/products/1415889>

Schematic diagram



Layout of connector pin assignments

Circuit diagram



Contact assignment of M8 plugs/sockets

# SAC-3P-M 8MS/1,5-PVC/M 8FR - Sensor/actuator cable



1415889

<https://www.phoenixcontact.com/us/products/1415889>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415889>



### UL Listed

Approval ID: FILE E 221474

|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | 60 V                  | 4 A                   | -                 | -                           |



### cUL Listed

Approval ID: FILE E 221474

|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | 60 V                  | 4 A                   | -                 | -                           |



### EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

# SAC-3P-M 8MS/1,5-PVC/M 8FR - Sensor/actuator cable



1415889  
<https://www.phoenixcontact.com/us/products/1415889>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

1415889  
<https://www.phoenixcontact.com/us/products/1415889>

Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |
| EF3.0 Climate Change                    |                                          |
| CO2e kg                                 | 0.432 kg CO2e                            |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)