

1416137

https://www.phoenixcontact.com/us/products/1416137

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PUR halogen-free, welding sputter-resistant, orange RAL 2003, Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 2 m, for robots and drag chains

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- · Reliable solution for the body shop as cable is welding sputter resistant

Commercial data

Item number	1416137
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF1CDA
GTIN	4055626063751
Weight per piece (including packing)	132.5 g
Weight per piece (excluding packing)	132.5 g
Country of origin	PL



1416137

https://www.phoenixcontact.com/us/products/1416137

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Robots and drag chains
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	A
Insulation characteristics	
Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	НВ
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	48 V AC
	60 V DC
Nominal current I _N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.4 Nm (M12 connector)

Connector

Connection 1



1416137

https://www.phoenixcontact.com/us/products/1416137

Туре	Plug straight M12
Number of positions	5
Coding type	A
Connection 2	
Connection 2 Type	Socket straight M12
	Socket straight M12 5

Cable/line

Cable length	2 m
--------------	-----

PUR, halogen-free, highly flexible, welding-sputter resistant, orange [810]

Dimensional drawing



Note	Due to the extremely robust outer sheath, this cable should only be stripped in 5 cm increments.
UL AWM Style	20549 (80°C/300 V)
Number of positions	5
Shielded	no
Cable type	PUR, halogen-free, highly flexible, welding-sputter resistant, orange [810]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	5x 0.34 mm²
Wire diameter incl. insulation	1.55 mm ±0.05 mm (Signal line)
External cable diameter	6.90 mm ±0.1 mm
Outer sheath, material	PUR
External sheath, color	orange RAL 2003
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black, green-yellow
Overall twist	5 wires around filler to the core
Max. conductor resistance	approx. 57 Ω/km
Insulation resistance	≥ 20 MΩ*km
Nominal voltage, cable	300 V (Peak value, not for high-power applications)
Test voltage Core/Core	3000 V (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D



1416137

https://www.phoenixcontact.com/us/products/1416137

Smallest bending radius, fixed installation	35 mm
Smallest bending radius, movable installation	69 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s², Ambient temperature: ≤ 60 °C
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in acc. with UL FT-2
Other resistance	hydrolysis and microbe resistant
Special properties	Sheath resistant to welding beads, can be recycled, matt, without adhesion, wear-resistant, flame resistant and self-extinguishing
	Free from silicone and cadmium
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C 80 °C (cable, fixed installation)
	-25 °C 80 °C (Cable, flexible installation)
	≤ 60 °C (cable, drag chain applications)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation) (male connector/female connector)	-25 °C 90 °C (Plug / socket)

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101




1416137

https://www.phoenixcontact.com/us/products/1416137


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight




1416137

https://www.phoenixcontact.com/us/products/1416137



Pin assignment M12 male connector, 5-pos., A-coded, male side



Pin assignment M12 socket, 5-pos., A-coded, socket side view



1416137

https://www.phoenixcontact.com/us/products/1416137

Circuit diagram



Contact assignment of the M12 plug and the M12 socket



1416137

https://www.phoenixcontact.com/us/products/1416137

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1416137

UL Listed Approval ID: FILE E 221474					
		Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
		125 V	4 A	-	-

cUL Listed Approval ID: FILE E 221					
		Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
		125 V	4 A	-	-

EHE	EAC-RoHS	
LIIL	Approval ID: RU D-DE.HB35.B.00387	



1416137

https://www.phoenixcontact.com/us/products/1416137

Classifications

_		
_	\sim 1	ΛCC
-		AOO

	ECLASS-13.0	27060311		
E.	ГІМ			
	ETIM 9.0	EC001855		
U	UNSPSC			
	UNSPSC 21.0	26121600		



1416137

https://www.phoenixcontact.com/us/products/1416137

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	1.57 kg CO2e

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com