

# SAC-4P-M12MS/10,0-PUR BK - Sensor/actuator cable



1563410

<https://www.phoenixcontact.com/us/products/1563410>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, on free cable end, cable length: 10 m

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1563410       |
| Packing unit                         | 5 pc          |
| Minimum order quantity               | 50 pc         |
| Product key                          | AF1CCA        |
| GTIN                                 | 4046356303286 |
| Weight per piece (including packing) | 305.5 g       |
| Weight per piece (excluding packing) | 309 g         |
| Country of origin                    | DE            |

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Number of positions  | 4                     |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |
| Outer sheath, material                 | PUR                                         |
| Conductor material                     | Bare Cu litz wires                          |

### Electrical properties

|                           |                           |
|---------------------------|---------------------------|
| Insulation resistance     | $\geq 10 \text{ M}\Omega$ |
| Nominal voltage $U_N$     | 250 V AC                  |
|                           | 250 V DC                  |
| Nominal current $I_N$     | 4 A                       |
| Max. conductor resistance | 58 $\Omega/\text{km}$     |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
| Max. bending cycles         | 4000000    |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connector

#### Connection 1

|                     |                   |
|---------------------|-------------------|
| Type                | Plug straight M12 |
| Number of positions | 4                 |

# SAC-4P-M12MS/10,0-PUR BK - Sensor/actuator cable



1563410

<https://www.phoenixcontact.com/us/products/1563410>

|             |   |
|-------------|---|
| Coding type | A |
|-------------|---|


## Connection 2

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

## Cable/line

|              |      |
|--------------|------|
| Cable length | 10 m |
|--------------|------|

## PUR halogen-free black [PUR]

|                                               |                                                                                                                         |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------|
| Dimensional drawing                           |                                       |
| Cable weight                                  | 30 kg/km                                                                                                                |
| UL AWM Style                                  | 20549 / 10493 (80°C/300 V)                                                                                              |
| Number of positions                           | 4                                                                                                                       |
| Shielded                                      | no                                                                                                                      |
| Cable type                                    | PUR halogen-free black [PUR]                                                                                            |
| Conductor structure signal line               | 42x 0.10 mm                                                                                                             |
| AWG signal line                               | 22                                                                                                                      |
| Conductor cross section                       | 4x 0.34 mm <sup>2</sup> (Signal line)                                                                                   |
| Wire diameter incl. insulation                | 1.27 mm ±0.02 mm                                                                                                        |
| External cable diameter                       | 4.20 mm ±0.15 mm                                                                                                        |
| Outer sheath, material                        | PUR                                                                                                                     |
| External sheath, color                        | black-gray RAL 7021                                                                                                     |
| Conductor material                            | Bare Cu litz wires                                                                                                      |
| Material wire insulation                      | PP                                                                                                                      |
| Single wire, color                            | brown, white, blue, black                                                                                               |
| Thickness, insulation                         | ≥ 0.21 mm                                                                                                               |
| Thickness, outer sheath                       | approx. 0.50 mm                                                                                                         |
| Overall twist                                 | 4 wires, twisted                                                                                                        |
| Max. conductor resistance                     | ≤ 58 Ω/km                                                                                                               |
| Insulation resistance                         | ≥ 1 GΩ*km                                                                                                               |
| Nominal voltage, cable                        | ≤ 300 V                                                                                                                 |
| Test voltage                                  | ≥ 3000 V                                                                                                                |
| Minimum bending radius, fixed installation    | 5 x D                                                                                                                   |
| Minimum bending radius, flexible installation | 10 x D                                                                                                                  |
| Smallest bending radius, fixed installation   | 21 mm                                                                                                                   |
| Smallest bending radius, movable installation | 42 mm                                                                                                                   |
| Dynamic load capacity (bending)               | Max. bending cycles: 10000000, Bending radius: 42 mm, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 |

1563410

<https://www.phoenixcontact.com/us/products/1563410>

|                                 |                                                                                                          |
|---------------------------------|----------------------------------------------------------------------------------------------------------|
|                                 | m/s, Acceleration: 10 m/s <sup>2</sup>                                                                   |
| Dynamic load capacity (torsion) | Torsion: $\pm 180^\circ/\text{m}$ , Torsion cycles: $\geq 2000000$ , Torsional frequency: 35 cycles/min. |
| Halogen-free                    | in accordance with DIN VDE 0472 part 815                                                                 |
|                                 | in accordance with DIN EN 50267-2-1                                                                      |
| Flame resistance                | in accordance with UL 758/1581 FT2                                                                       |
|                                 | DIN EN 60332-2-2 (20 s)                                                                                  |
| Resistance to oil               | in accordance with DIN EN 60811-2-1                                                                      |
| Other resistance                | Highly resistant to acids, alkaline solutions and solvents                                               |
|                                 | hydrolysis and microbe resistant                                                                         |
|                                 | partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)                                             |
|                                 | Low adhesion                                                                                             |
|                                 | abrasion-resistant                                                                                       |
| Special properties              | Flexible cable conduit capable                                                                           |
|                                 | Silicone-free                                                                                            |
|                                 | Free of substances which would hinder coating with paint or varnish                                      |
|                                 | flexible                                                                                                 |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)                                                             |
|                                 | -25 °C ... 80 °C (Cable, flexible installation)                                                          |


## Environmental and real-life conditions

### Ambient conditions

|                                 |                                                |
|---------------------------------|------------------------------------------------|
| Degree of protection            | IP65                                           |
|                                 | IP67                                           |
|                                 | IP68                                           |
| Ambient temperature (operation) | -25 °C ... 90 °C (Plug / socket)               |
|                                 | -40 °C ... 80 °C (cable, fixed installation)   |
|                                 | -5 °C ... 80 °C (Cable, flexible installation) |

## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

1563410


<https://www.phoenixcontact.com/us/products/1563410>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

Circuit diagram



Contact assignment of the M12 plug

# SAC-4P-M12MS/10,0-PUR BK - Sensor/actuator cable



1563410

<https://www.phoenixcontact.com/us/products/1563410>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
|-------------|----------|

# SAC-4P-M12MS/10,0-PUR BK - Sensor/actuator cable



1563410

<https://www.phoenixcontact.com/us/products/1563410>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)