

# UC-19S1N12R3DU - Cable connector



1606701

<https://www.phoenixcontact.com/us/products/1606701>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: UC, straight, shielded: yes, Screw locking mechanism, No. of pos. : 16+3, Direction of rotation: Standard, contact connection type: Socket, Solder cup, cable diameter range: 2 mm ... 14.5 mm, coding: N, this item is expected to be lead-free from Q4 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1606701
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAIA
GTIN	4046356261296
Weight per piece (including packing)	128.6 g
Weight per piece (excluding packing)	111.998 g
Customs tariff number	85366990
Country of origin	DE

# UC-19S1N12R3DU - Cable connector



1606701

<https://www.phoenixcontact.com/us/products/1606701>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Material specifications

Housing material	Metal
------------------	-------

### Connector

#### Insulating body

Coding	N
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+3
Number Contact (Contact group 1)	3
Diameter Contact (Contact group 1)	1.5 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm <sup>2</sup>
Litz wire cross-section max. Contact (Contact group 1)	1 mm <sup>2</sup>
Rated current Contact (Contact group 1)	10 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Contact group 2)	16
Diameter Contact (Contact group 2)	1 mm
Litz wire cross-section min. Contact (Contact group 2)	0.08 mm <sup>2</sup>
Litz wire cross-section max. Contact (Contact group 2)	1 mm <sup>2</sup>
Rated current per data contact at 25°C	8 A

#### Housing

Thread type	M23
Type of locking	Screw locking mechanism
Pg screw connection	Pg13,5
Housing material	GD-Zn
Degree of protection (plugged in)	IP67

#### Seal

# UC-19S1N12R3DU - Cable connector



1606701

<https://www.phoenixcontact.com/us/products/1606701>

External cable diameter	2 mm ... 14.5 mm
Seal material	NBR

# UC-19S1N12R3DU - Cable connector


1606701

<https://www.phoenixcontact.com/us/products/1606701>



## Drawings

Schematic diagram



Connector pin assignment


# UC-19S1N12R3DU - Cable connector

1606701

<https://www.phoenixcontact.com/us/products/1606701>



Schematic diagram



Connector pin assignment


# UC-19S1N12R3DU - Cable connector

1606701

<https://www.phoenixcontact.com/us/products/1606701>



Schematic diagram




Dimensional drawing

# UC-19S1N12R3DU - Cable connector



1606701

<https://www.phoenixcontact.com/us/products/1606701>



# UC-19S1N12R3DU - Cable connector



1606701

<https://www.phoenixcontact.com/us/products/1606701>

## Classifications

### ECLASS

ECLASS-13.0	27440116
-------------	----------

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------



# UC-19S1N12R3DU - Cable connector



1606701

<https://www.phoenixcontact.com/us/products/1606701>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9b3f5bf4-79b5-46a1-a350-d72211adbca6

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)