

RF-17M1N1290DU - Coupler connector



1616607

<https://www.phoenixcontact.com/us/products/1616607>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, straight, Screw locking mechanism, M23, number of positions: 17, contact connection type: Pin, shielded: yes, cable diameter range: 5 mm ... 13.2 mm, number of positions: 17, connection method: Solder connection, series: RF

Commercial data

Item number	1616607
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAGG
GTIN	4046356601870
Weight per piece (including packing)	103.39 g
Weight per piece (excluding packing)	99.01 g
Country of origin	DE

RF-17M1N1290DU - Coupler connector



1616607

<https://www.phoenixcontact.com/us/products/1616607>

Technical data

Product properties

Product type	Circular connector (cable-side)
Series	RF
Application	Signal
Number of positions	17
Connection profile	17
Shielded	yes
Coding	N
Thread type	M23

Material specifications

Seal material	FPM
Housing material	Metal

Connection data

Conductor connection

Connection method	Solder connection
-------------------	-------------------

Electrical properties

Contact

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Max. current	8 A
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

Connector

Type	straight
Direction of rotation	Standard

Cable/line

External cable diameter	5 mm ... 13.2 mm
-------------------------	------------------

Environmental and real-life conditions

RF-17M1N1290DU - Coupler connector



1616607

<https://www.phoenixcontact.com/us/products/1616607>

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m


RF-17M1N1290DU - Coupler connector

1616607


<https://www.phoenixcontact.com/us/products/1616607>

Drawings

Dimensional drawing



Dimensional drawing




RF-17M1N1290DU - Coupler connector

1616607

<https://www.phoenixcontact.com/us/products/1616607>

Schematic diagram



RF-17M1N1290DU - Coupler connector



1616607

<https://www.phoenixcontact.com/us/products/1616607>

Classifications

UNSPSC

UNSPSC 21.0	39121413
-------------	----------

RF-17M1N1290DU - Coupler connector



1616607

<https://www.phoenixcontact.com/us/products/1616607>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com