

# K-3E - OE/12,5-B01/M17 F8 - S - Signal and power cable



1627727

<https://www.phoenixcontact.com/us/products/1627727>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



## Commercial data

Item number	1627727
Packing unit	1 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Product key	ABRDBA
GTIN	4055626347295
Weight per piece (including packing)	2,252 g
Weight per piece (excluding packing)	2,252 g
Country of origin	DE

# K-3E - OE/12,5-B01/M17 F8 - S - Signal and power cable



1627727

<https://www.phoenixcontact.com/us/products/1627727>

## Technical data

### Notes

#### Safety note

##### Safety note

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.

- WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

- The products are suitable for applications in plant, controller, and electrical device engineering.

- When operating the connectors in outdoor applications, they must be separately protected against environmental influences.

- Assembled products may not be manipulated or improperly opened.

- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).

- When using the product in direct connection with third-party manufacturers, the user is responsible.

- For operating voltages > 50 V AC, conductive connector housings must be grounded

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- Only use tools recommended by Phoenix Contact

- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.

- Operate the connector only when it is fully plugged in and interlocked.

- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

# K-3E - OE/12,5-B01/M17 F8 - S - Signal and power cable



1627727

<https://www.phoenixcontact.com/us/products/1627727>

## Product properties

Product type	Signal and power cable
Number of positions	4
Coding	N
Thread type	M17

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 105 °C

## Connector

Type	plastic molded
Direction of rotation	Standard

## Electrical properties

### Contact

Nominal voltage $U_N$	630 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	6 kV

## Material specifications

Insulator material	PA 6.6
Contact material	CuZn
Contact surface	Ni/Au

## Connection data

Connection method	Cable
-------------------	-------


# K-3E - OE/12,5-B01/M17 F8 - S - Signal and power cable



1627727

<https://www.phoenixcontact.com/us/products/1627727>

## Drawings



$I$  = current strength,  $\vartheta$  = ambient temperature,  $3 \times 25 \text{ A}$

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)