

UCT-TM 4 VT CUS - Marker for terminal blocks



0829592

<https://www.phoenixcontact.com/us/products/0829592>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker for terminal blocks, can be ordered: by sheet, violet, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 4.2 mm, Number of individual labels: 84



Your advantages

- The UCT-TM... UniCard labeling range includes markers for Phoenix Contact products with tall marker grooves, e.g. terminals
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications
- The multi-section marking strips are easy to fit and can be easily separated if required
- The sheets provide space for including function texts

Commercial data

Item number	0829592
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8118
GTIN	4046356597418
Weight per piece (including packing)	14.089 g
Weight per piece (excluding packing)	13.5 g
Country of origin	PL

UCT-TM 4 VT CUS - Marker for terminal blocks



0829592

<https://www.phoenixcontact.com/us/products/0829592>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	4.2 mm

Marking

Number of individual labels	84
Number of individual labels per row	14
Identification technology	Thermal transfer for sheets and cards

Mounting

Mounting type	snap into tall marker groove
---------------	------------------------------

Material specifications

RoHS compliant	yes
Color	violet (RAL 4005)
Material	PC
Flammability rating according to UL 94	V0
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Shelf life	2 years

Dimensions

Width	3.60 mm
Height	10.50 mm
Depth	4.60 mm
Pitch	4.2 mm
Length	10.5 mm

Standards and regulations


Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Notes

General	Can be labeled via thermal transfer
---------	-------------------------------------

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

UCT-TM 4 VT CUS - Marker for terminal blocks



0829592

<https://www.phoenixcontact.com/us/products/0829592>

Classifications

ETIM

ETIM 8.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT-TM 4 VT CUS - Marker for terminal blocks



0829592
<https://www.phoenixcontact.com/us/products/0829592>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com