

# WMTB HF (55X25)R - Cable marker



0830411

<https://www.phoenixcontact.com/us/products/0830411>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Roll, white, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: Assembly with cable ties, cable diameter:  $\geq 6$  mm, Number of individual labels: 500, text field height: 25 mm, text field width: 55 mm

## Your advantages

- The WMTB HF ... conductor and cable marking is used for the identification and bundling conductors and cables indoors and outdoors
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The markers are made of a halogen-free material
- The highly flexible material adapts to the conductors and cables

## Commercial data

Item number	0830411
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG15
Product key	BG2311
GTIN	4046356716031
Weight per piece (including packing)	1,028.2 g
Weight per piece (excluding packing)	987.8 g
Customs tariff number	39204910
Country of origin	DK

# WMTB HF (55X25)R - Cable marker



0830411

<https://www.phoenixcontact.com/us/products/0830411>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Number of individual labels	500
Number of individual labels per row	1
Identification technology	Thermal transfer for rolls

### Dimensions

Width	75 mm
Height	24.3 mm
Depth	0.6 mm

### Material specifications

RoHS compliant	yes
Color	white (RAL 9010)
Material	PUR
Flammability rating according to UL 94	V2 (0,75 mm Wandstärke)
Components	halogen-free

### Cable/line

External cable diameter	≥ 6.00 mm
-------------------------	-----------

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

# WMTB HF (55X25)R - Cable marker



0830411

<https://www.phoenixcontact.com/us/products/0830411>

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
IRM 901	Test passed
IRM 902	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Ambient conditions

Ambient temperature (operation)	-25 °C ... 100 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	10 °C ... 25 °C
Recommended humidity (storage/transport)	45 % ... 55 %
Shelf life	2 years

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

# WMTB HF (55X25)R - Cable marker



0830411

<https://www.phoenixcontact.com/us/products/0830411>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 9.0	EC001530
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# WMTB HF (55X25)R - Cable marker



0830411  
<https://www.phoenixcontact.com/us/products/0830411>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)