

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable



1669039

<https://www.phoenixcontact.com/us/products/1669039>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, on Socket angled M12, coding: A, with 2 LEDs, PIN 2+4 bridged and Socket angled M12, coding: A, with 2 LEDs, PIN 2+4 bridged, cable length: 0.3 m

Commercial data

Item number	1669039
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF03
Product key	AF1COA
GTIN	4017918136000
Weight per piece (including packing)	48.6 g
Weight per piece (excluding packing)	49 g
Customs tariff number	85444290
Country of origin	PL

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable



1669039

<https://www.phoenixcontact.com/us/products/1669039>

Technical data

Product properties

Product type	Distributor with cable
Application	Standard
Number of positions	3
No. of cable outlets	2
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Connection data

Tightening torque	0.4 Nm (M12 connector)
-------------------	------------------------

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	24 V DC
Nominal current I_N	4 A
Test voltage	2500 V

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	2 LEDs
Status display present	yes

Connector

Connection 1

Type	Plug straight M12
------	-------------------

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable



1669039

<https://www.phoenixcontact.com/us/products/1669039>

Coding type	A
-------------	---

Connection 2

Type	Socket angled M12
Coding type	A

Connection 3

Type	Socket angled M12
Coding type	A

Cable/line

Cable length	0.3 m
--------------	-------

PUR halogen-free black [PUR]

Dimensional drawing		
Cable weight	23 kg/km	
UL AWM Style	20549	
Number of positions	3	
Shielded	no	
Cable type	PUR halogen-free black [PUR]	
Conductor structure signal line	42x 0.10 mm	
AWG signal line	22	
Conductor cross section	3x 0.34 mm ² (Signal line)	
Wire diameter incl. insulation	1.27 mm ±0.02 mm (Signal line)	
External cable diameter	3.85 mm ±0.15 mm	
Outer sheath, material	PUR	
External sheath, color	black-gray RAL 7021	
Conductor material	Bare Cu litz wires	
Material wire insulation	PP	
Single wire, color	brown, blue, black	
Thickness, insulation	≥ 0.21 mm (Core insulation)	
	approx. 0.50 mm (Outer cable sheath)	
Overall twist	3 wires, twisted	
Max. conductor resistance	max. 58 Ω/km (at 20 °C)	
Insulation resistance	≥ 100 GΩ*km (at 20 °C)	
Nominal voltage, cable	≤ 300 V	
Test voltage	≥ 3000 V	
Smallest bending radius, fixed installation	19 mm	

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable



1669039

<https://www.phoenixcontact.com/us/products/1669039>

Smallest bending radius, movable installation	38 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 38 mm, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥2000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67 IP68
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	-5 °C ... 80 °C (Cable, flexible installation)

Standards and regulations

M12

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable



1669039

<https://www.phoenixcontact.com/us/products/1669039>

Drawings

Dimensional drawing



Plug M12 x 1, Y distributor

Dimensional drawing



Socket M12 x 1, angled, with LED

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable

1669039

<https://www.phoenixcontact.com/us/products/1669039>

Schematic diagram




Pin assignment M12 Y plug, 4-pos., A-coded, view plug side

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable

1669039


<https://www.phoenixcontact.com/us/products/1669039>

Schematic diagram



Pin assignment M12 socket, 3-pos., PIN 2+4 bridged, A-coded, view female side

Circuit diagram



Contact assignment of the M12 plug and the M12 socket, with LEDs, bridged

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable



1669039

<https://www.phoenixcontact.com/us/products/1669039>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1669039>



UL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	24 V	4 A	-	-



cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	24 V	4 A	-	-



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable



1669039

<https://www.phoenixcontact.com/us/products/1669039>

Classifications

ECLASS

ECLASS-13.0	27060313
-------------	----------

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-M12Y/2X0,3-PUR/M12FR2LB - Sensor/actuator cable



1669039
<https://www.phoenixcontact.com/us/products/1669039>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.441 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com