

UCT4-EMLP (27X12,5) SR - Plastic label



1056550
<https://www.phoenixcontact.com/us/products/1056550>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plastic label, Sheet, silver, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, text field height: 12.5 mm, text field width: 27 mm

Your advantages

- The UCT4-EM(L)P... device markers are suitable for gluing into or latching into the SIEMENS SIRIUS ACT 3SU... button series marker carriers
- The markers, which are supplied in uniform sheets, can be marked quickly, easily, and precisely using the card printers
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	1056550
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG2418
GTIN	4055626697420
Weight per piece (including packing)	7.51 g
Weight per piece (excluding packing)	7.56 g
Country of origin	PL

UCT4-EMLP (27X12,5) SR - Plastic label



1056550

<https://www.phoenixcontact.com/us/products/1056550>

Technical data

Product properties

Product type	Gerätemarker
Area of application	SIEMENS: SIRIUS ACT 3SU marker carrier

Marking

Identification technology	Thermal transfer for sheets and cards, UV LED technology, direct laser marking
---------------------------	--

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	silver
Material	PC
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	26.65 mm
Height	12.40 mm
Depth	0.80 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

UCT4-EMLP (27X12,5) SR - Plastic label



1056550

<https://www.phoenixcontact.com/us/products/1056550>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT4-EMLP (27X12,5) SR - Plastic label



1056550
<https://www.phoenixcontact.com/us/products/1056550>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.167 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com