

1343027

<https://www.phoenixcontact.com/us/products/1343027>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ethernet switch, twenty-four RJ45 ports with 10/100 Mbps on all ports, automatic data transmission speed detection, autocrossing function, and QoS

Your advantages

- QoS-prioritized (Quality of Service) messages
- RJ45 ports support a transmission speed of 10/100 Mbps
- Local diagnostic indicators with LEDs
- PROFINET PTCP filter for reliable communication on PROFINET networks
- Enhanced traffic prioritization for automation protocols
- Energy-efficient Ethernet in accord. with IEEE 802.3az
- PROFINET Conformance Class A for real-time data exchange
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial data

Item number	1343027
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN20
Product key	DNN116
GTIN	4063151654511
Weight per piece (including packing)	729.6 g
Weight per piece (excluding packing)	620 g
Customs tariff number	85176200
Country of origin	TW

FL SWITCH 1024T - Industrial Ethernet Switch



1343027

<https://www.phoenixcontact.com/us/products/1343027>

Technical data

Dimensions

Width	65 mm
Height	141 mm
Depth	107 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Housing material	Polycarbonate fiber reinforced
	Aluminum / steel sheet DC01

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Interfaces

Ethernet (RJ45)

Number of interfaces	24
Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	24 (RJ45 ports)
Input buffer	4 Mbits
Output buffer	4 Mbits

Product properties

Product type	Switch
Product family	Unmanaged Switch 1000
MTTF	32.9 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
	388.4 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	354.1 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
Special properties	Extended temperature range
Basic functions	Unmanaged switch
	Autonegotiation
	Store and Forward switching mode

FL SWITCH 1024T - Industrial Ethernet Switch



1343027

<https://www.phoenixcontact.com/us/products/1343027>

Switch functions

Basic functions	Unmanaged switch
	Autonegotiation
	Store and Forward switching mode
MAC address table	8k
Status and diagnostic indicators	LEDs: U _S , link and activity per port
Additional functions	100 BASE-TX/100BASE-FX (IEEE 802.3u)
	Quality of Service (QoS) prioritization (IEEE 802.1p)
	Energy-efficient Ethernet (IEEE 802.3az)
	10Base-T (IEEE 802.3)

Security functions

Basic functions	Unmanaged switch
	Autonegotiation
	Store and Forward switching mode

Electrical properties

Maximum power dissipation for nominal condition	3.6 W (at 24 V DC)
Transmission medium	Copper

Supply

Supply voltage (DC)	24 V
Supply voltage (AC)	24 V AC (50/60 Hz)
Supply voltage range	9 V DC ... 32 V DC
	18 V AC ... 30 V AC (50/60 Hz)
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	400 mA (at 9 V DC)
Typical current consumption	56 mA (at 24 V DC)

Connection data

Connection technology

Connection name	Power supply
pluggable	yes

Power supply

Connection method	Push-in spring connection
Conductor cross-section, rigid	0.5 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section AWG	20 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible, with ferrule without plastic sleeve	0.5 mm ² ... 2.5 mm ²
Stripping length	10 mm

FL SWITCH 1024T - Industrial Ethernet Switch



1343027

<https://www.phoenixcontact.com/us/products/1343027>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	2000 m (maximum)
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock (operation)	30g (EN 60068-2-27)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)
Air pressure (storage/transport)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)

Approvals

Conformity/Approvals

Conformance	CE-compliant
UL, USA / Canada	UL 61010-1, UL 61010-2-201 Class I, Div. 2, Groups A, B, C, D, T4 Class I, Zone 2, Group IIC, T4
FCC	Title 47 Part 15 Subpart B:2018 Class A

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	EN 61000-6-2 EN 61000-4-2 (ESD) Criterion B
	EN 61000-6-2 EN 61000-4-3 (electromagnetic fields) Criterion A
	EN 61000-6-2 EN 61000-4-4 (EFT burst) Criterion A
	EN 61000-6-2 EN 61000-4-5 (surge) Criterion B
	EN 61000-6-2 EN 61000-4-6 (line noise immunity) Criterion A
	EN 61000-6-2 EN 61000-4-8 (electromagnetic fields) Criterion A
Noise immunity	EN 61000-6-2 Class A
	EN 61000-6-2:2019

Noise emission

Standards/regulations	EN_61000-6-4:2019
-----------------------	-------------------

System properties

Functionality

Basic functions	Unmanaged switch
	Autonegotiation
	Store and Forward switching mode

Signaling

FL SWITCH 1024T - Industrial Ethernet Switch



1343027

<https://www.phoenixcontact.com/us/products/1343027>

Status display	LEDs: U _S , link and activity per port
----------------	---

FL SWITCH 1024T - Industrial Ethernet Switch



1343027

<https://www.phoenixcontact.com/us/products/1343027>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1343027>

 **KC**
Approval ID: R-R-PCK-1343027

 **DNV GL**
Approval ID: TAA000034U

 **cULus Listed**
Approval ID: E238705

 **IECEx**
Approval ID: IECEx UL 22.0104X

 **ATEX**
Approval ID: UL 22 ATEX 2910X

 **cUL Listed**
Approval ID: E196811

 **UL Listed**
Approval ID: E196811

FL SWITCH 1024T - Industrial Ethernet Switch



1343027

<https://www.phoenixcontact.com/us/products/1343027>

Classifications

ECLASS

ECLASS-13.0	19170402
ECLASS-15.0	19170402

ETIM

ETIM 9.0	EC000734
----------	----------

FL SWITCH 1024T - Industrial Ethernet Switch



1343027

<https://www.phoenixcontact.com/us/products/1343027>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: n/a)
SCIP	3f0669ce-afd8-4e89-bbee-3e1df1028fe3

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com