

# VS-M12MS-M12FS-915-LI/1,0 - Bus system cable



1403546

<https://www.phoenixcontact.com/us/products/1403546>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, PROFIBUS, 2-pos., green halogen-free PUR, shielded, straight M12 B-coded male plug to straight M12 B-coded female plug, length: 1 m

## Commercial data

Item number	1403546
Packing unit	1 pc
Minimum order quantity	25 pc
Note	Made to order (non-returnable)
Product key	AF1CJC
GTIN	4046356657112
Weight per piece (including packing)	111.4 g
Weight per piece (excluding packing)	103.3 g
Country of origin	PL

# VS-M12MS-M12FS-915-LI/1,0 - Bus system cable



1403546

<https://www.phoenixcontact.com/us/products/1403546>

## Technical data

### Product properties

Product type	Data cable preassembled
Number of positions	2
No. of cable outlets	1
Shielded	yes
Coding	B

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Signaling

Status display	no
Status display present	no

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	4 A

### Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

### Connector

#### Connection 1

Type	Plug straight M12
Number of positions	2
Coding type	B (inverse)

#### Connection 2

Type	Socket straight M12
Number of positions	2

### Cable/line

Cable length	1 m
--------------	-----

# VS-M12MS-M12FS-915-LI/1,0 - Bus system cable



1403546

<https://www.phoenixcontact.com/us/products/1403546>

## PROFIBUS [915]

Cable weight	74 kg/km
Number of positions	2
Shielded	yes
Cable type	PROFIBUS [915]
Conductor structure	1x2xAWG24/19
Conductor structure signal line	19x 0.14 mm
AWG signal line	24
Conductor cross section	2x 0.25 mm²
Wire diameter incl. insulation	2.56 mm
External cable diameter	8.00 mm ±0.4 mm
Outer sheath, material	PUR
External sheath, color	blue
Conductor material	Bare Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	red, green
Thickness, outer sheath	approx. 0.80 mm
Overall twist	2 wires, twisted
Optical shield covering	70 %
Insulation resistance	≥ 16 GΩ*km
Working capacitance	28 nF (at 1 kHz)
Nominal voltage, cable	≤ 100 V
Test voltage Core/Core	3600 V DC
Minimum bending radius, flexible installation	5 x D
Smallest bending radius, movable installation	40 mm
Dynamic load capacity (bending)	Max. bending cycles: 3000000, Bending radius: 60 mm, Acceleration: 4 m/s²
Tensile strength	≤ 100 N
Flame resistance	according to IEC 60332-1
Resistance to oil	Resistant to mineral oils and grease
Ambient temperature (operation)	-40 °C ... 80 °C (Cable, flexible installation)


## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-20 °C ... 80 °C (Cable, flexible installation)


## Drawings

Dimensional drawing




Plug, M12 x 1, straight, shielded

Dimensional drawing




M12 x 1 socket, straight, shielded

Schematic diagram




Pin assignment M12 male connector, 5-pos., B-coded, male side

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side

Circuit diagram



# VS-M12MS-M12FS-915-LI/1,0 - Bus system cable



1403546

<https://www.phoenixcontact.com/us/products/1403546>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### ETIM

ETIM 9.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# VS-M12MS-M12FS-915-LI/1,0 - Bus system cable



1403546

<https://www.phoenixcontact.com/us/products/1403546>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)