

MCS-156X127-C-L-5015 - Housing frame



1524428

<https://www.phoenixcontact.com/us/products/1524428>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing frame, Latching cover (non-detachable), color: blue (similar RAL 5015)

Your advantages

- Convenient operation during device installation and maintenance thanks to optional hinges on the housing cover
- Flexible mounting thanks to the optional adapter plate
- Safe operation with the right degree of protection
- Individualized product selection due to the modular system
- Optimized PCB installation: PCB can be installed in a nearly horizontal orientation thanks to the angled housing edge

Commercial data

Item number	1524428
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AC04
Product key	ACFFAB
GTIN	4063151991654
Weight per piece (including packing)	93.54 g
Weight per piece (excluding packing)	64.95 g
Customs tariff number	84879090
Country of origin	DE

MCS-156X127-C-L-5015 - Housing frame



1524428

<https://www.phoenixcontact.com/us/products/1524428>

Technical data

Notes

Assembly note	Please observe the assembly instructions available in the download area.
Recommendation	Further information and detailed dimensions are available in the download area.

Product properties

Product type	Cover
Housing type	Field housing
Housing series	MCS
Product family	MCS-156X127
Ventilation openings present	no

Dimensions

Dimensional drawing	
Dimensions	157.2 mm x 128.2 mm x 13.4 mm 134.2 mm x 97.1 mm x 5.9 mm

Material specifications

Color (Housing)	blue (RAL 5015)
Color (Window)	transparent
Material (Housing)	PA-GF
Material (Window)	PC
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Glow-wire test

MCS-156X127-C-L-5015 - Housing frame



1524428

<https://www.phoenixcontact.com/us/products/1524428>

Specification	IEC 60695-2-11:2021-10
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	10

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Test for substances that would hinder coating with paint or varnish

Specification	VDMA 24364:2018-05
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 85 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Latching
Mounting position	any

Packaging specifications

Type of packaging	Box packaging
-------------------	---------------

MCS-156X127-C-L-5015 - Housing frame

1524428

<https://www.phoenixcontact.com/us/products/1524428>



Drawings

Dimensional drawing



Schematic representation – for additional information, see product range drawing in the Download Center

MCS-156X127-C-L-5015 - Housing frame



1524428

<https://www.phoenixcontact.com/us/products/1524428>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

MCS-156X127-C-L-5015 - Housing frame



1524428

<https://www.phoenixcontact.com/us/products/1524428>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com