

RC-09S1N12K0M6 - Cable connector



1596116

<https://www.phoenixcontact.com/us/products/1596116>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: RC, straight plastic-sheathed, shielded: yes, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Socket, Solder cup, cable diameter range: 9.5 mm ... 10.5 mm, coding: N

Commercial data

Item number	1596116
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356209861
Weight per piece (including packing)	41.63 g
Weight per piece (excluding packing)	41.63 g
Country of origin	DE

RC-09S1N12K0M6 - Cable connector



1596116

<https://www.phoenixcontact.com/us/products/1596116>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number Contact (Contact group 1)	1
Diameter Contact (Contact group 1)	2 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number Contact (Contact group 2)	8
Diameter Contact (Contact group 2)	1 mm
Litz wire cross-section min. Contact (Contact group 2)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 2)	48 V AC
	48 V AC

Housing

Type	Cable connector housing
Thread type	M23
Design	straight plastic-sheathed
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn

RC-09S1N12K0M6 - Cable connector



1596116

<https://www.phoenixcontact.com/us/products/1596116>

Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67
Seal	
External cable diameter	9.5 mm ... 10.5 mm


RC-09S1N12K0M6 - Cable connector

1596116

<https://www.phoenixcontact.com/us/products/1596116>

Drawings

Schematic diagram



Connector pin assignment


RC-09S1N12K0M6 - Cable connector

1596116

<https://www.phoenixcontact.com/us/products/1596116>



Schematic diagram




Connector pin assignment

RC-09S1N12K0M6 - Cable connector

1596116

<https://www.phoenixcontact.com/us/products/1596116>

Schematic diagram



Dimensional drawing

RC-09S1N12K0M6 - Cable connector



1596116

<https://www.phoenixcontact.com/us/products/1596116>

Classifications

UNSPSC

UNSPSC 21.0	39121413
-------------	----------

RC-09S1N12K0M6 - Cable connector



1596116
<https://www.phoenixcontact.com/us/products/1596116>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com