

RC-12P2S8A90GU - Coupler connector



1598391

<https://www.phoenixcontact.com/us/products/1598391>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Crimp connection, cable diameter range: 5.5 mm ... 6.5 mm

Commercial data

Item number	1598391
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFG
GTIN	4046356220576
Weight per piece (including packing)	70.795 g
Weight per piece (excluding packing)	66.45 g
Country of origin	DE

RC-12P2S8A90GU - Coupler connector



1598391

<https://www.phoenixcontact.com/us/products/1598391>

Technical data

Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Connection method	Crimp connection
Application	Signal
Number of positions	12
Connection profile	12
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC

Housing

Type	Coupling housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67

Seal

External cable diameter	5.5 mm ... 6.5 mm
Seal material	NBR

RC-12P2S8A90GU - Coupler connector

1598391

<https://www.phoenixcontact.com/us/products/1598391>



Drawings

RC-12P2S8A90GU - Coupler connector



1598391

<https://www.phoenixcontact.com/us/products/1598391>

Classifications

UNSPSC

UNSPSC 21.0	39121413
-------------	----------

RC-12P2S8A90GU - Coupler connector



1598391

<https://www.phoenixcontact.com/us/products/1598391>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com