

UCS DIN 145-F 7035 - DIN rail adapter



2203839

<https://www.phoenixcontact.com/us/products/2203839>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail adapter for mounting one UCS 145-125-F housing (long side) or UCS 195-145-F housing (short side) onto an NS 35 DIN rail; will be set into the housing instead of a UCS SW 145 side wall; material: polycarbonate; color: light gray, similar to RAL 7035



Your advantages

- Practical customization options
- Tool-free snap-in principle enables easy mounting on the device panel
- Flexible mounting options for the control cabinet and use in the field
- Can be adapted to suit the application, thanks to identical receptacles in the housing
- Different colors for high recognition value inside and outside the control cabinet

Commercial data

Item number	2203839
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC03
Product key	ACFCAZ
GTIN	4055626540313
Weight per piece (including packing)	25.7 g
Weight per piece (excluding packing)	25 g
Customs tariff number	39269097
Country of origin	DE

UCS DIN 145-F 7035 - DIN rail adapter



2203839

<https://www.phoenixcontact.com/us/products/2203839>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
General	NOTE: Observe the maximum permissible total weight.

Product properties

Product type	DIN rail adapter
Housing type	Universal housings
Housing series	UCS
Type	Flat design
Ventilation openings present	no

Dimensions

Width	39.5 mm
Height	130.2 mm
Depth	23.9 mm
Depth from top edge of DIN rail	16.9 mm

Material specifications

Color (Housing)	light gray (RAL 7035)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	225
Insulating material	PC
Housing material	PC
Surface characteristics	untreated

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
---------------	------------------------

UCS DIN 145-F 7035 - DIN rail adapter



2203839

<https://www.phoenixcontact.com/us/products/2203839>

Temperature	125 °C
Test duration	1 h
Force	20 N

Mechanical strength / tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Frequency	50

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Test for substances that would hinder coating with paint or varnish

Specification	VW PV 3.10.7:2005-02
Result	Test passed

Degree of protection (IP code)

Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
Result, degree of protection, IP code	IP40

Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

Mounting

Mounting type	DIN rail mounting
Mounting position	On horizontal DIN rail NS 35/7.5 and NS 35/15 acc. to EN 60715

Packaging specifications

Type of packaging	PE bag
-------------------	--------

UCS DIN 145-F 7035 - DIN rail adapter

2203839

<https://www.phoenixcontact.com/us/products/2203839>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2203839>



UL Recognized

Approval ID: E240868

UCS DIN 145-F 7035 - DIN rail adapter



2203839

<https://www.phoenixcontact.com/us/products/2203839>

Classifications

ECLASS

ECLASS-13.0	27370419
-------------	----------

ETIM

ETIM 9.0	EC001024
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UCS DIN 145-F 7035 - DIN rail adapter



2203839

<https://www.phoenixcontact.com/us/products/2203839>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	Perfluorobutane sulfonic acid (PFBS) and its salts(CAS: n/a)

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com