

VIP-3/SC/HD62SUB/F - Termination board



2322430

<https://www.phoenixcontact.com/us/products/2322430>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and high density D-SUB miniature socket strip, for mounting on NS 35 rails, no. of pos.: 62, width: 180 mm

Your advantages

- Screw connection
- 1:1 connection

Commercial data

Item number	2322430
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C423
Product key	DK2112
GTIN	4046356451260
Weight per piece (including packing)	315.1 g
Weight per piece (excluding packing)	313.4 g
Customs tariff number	85366990
Country of origin	US

VIP-3/SC/HD62SUB/F - Termination board



2322430

<https://www.phoenixcontact.com/us/products/2322430>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	62

Electrical properties

Nominal voltage U_N	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A

Connection data

Connection 1 (control level)

Connection method	High-density D-SUB socket strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	62

Connection 2 (field level)

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of positions	63
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	113.5 mm
Height	69 mm
Depth	62 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

VIP-3/SC/HD62SUB/F - Termination board



2322430

<https://www.phoenixcontact.com/us/products/2322430>

Housing insulation material	Polyamide PA non-reinforced
-----------------------------	-----------------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	EN 50178
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--


VIP-3/SC/HD62SUB/F - Termination board

2322430

<https://www.phoenixcontact.com/us/products/2322430>



Drawings




VIP-3/SC/HD62SUB/F - Termination board

2322430

<https://www.phoenixcontact.com/us/products/2322430>



Circuit diagram



Universal circuit diagram

VIP-3/SC/HD62SUB/F - Termination board



2322430

<https://www.phoenixcontact.com/us/products/2322430>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2322430>

	cUL Recognized Approval ID: E238705			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	125 V	1 A	30 - 12	-

	UL Recognized Approval ID: E238705			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	125 V	1 A	30 - 12	-

VIP-3/SC/HD62SUB/F - Termination board



2322430

<https://www.phoenixcontact.com/us/products/2322430>

Classifications

ECLASS

ECLASS-13.0	27141152
-------------	----------

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-3/SC/HD62SUB/F - Termination board



2322430

<https://www.phoenixcontact.com/us/products/2322430>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	13539dff-f79b-4025-9b86-a9372068624c

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com